



Dimensions in inches (mm)

NW / KF Flange

| No. of Pins | INSTALLATION | A | B | C | D | P.C.D. | REFERENCE | PART NUMBER |
|-------------|--------------|--------------|------------|----------------|----------------|-------------|------------|-------------|
| 1 | NW / KF 16 | 1.18 (30) | .24 (6) | 2.19 (55.5) | 1.75 (44.5) | — (—) | N25K22A1CU | 12151 |
| 2 | NW / KF 16 | 1.18 (30) | .24 (6) | 1.89 (48) | 2.05 (52) | .32 (8) | N25K22A2CU | 11074 |
| 4 | NW / KF 16 | 1.18 (30) | .24 (6) | 1.89 (48) | 2.05 (52) | .40 (10) | N25K22A4CU | 12152 |
| 1 | NW / KF 25 | 1.57 (40) | .24 (6) | 2.19 (55.5) | 1.75 (44.5) | — (—) | N35K22A1CU | 11097 |
| 2 | NW / KF 25 | 1.57 (40) | .24 (6) | 2.19 (55.5) | 1.75 (44.5) | .32 (8) | N35K22A2CU | 11098 |
| 4 | NW / KF 25 | 1.57 (40) | .24 (6) | 2.19 (55.5) | 1.75 (44.5) | .40 (10) | N35K22A4CU | 11099 |

ConFlat® Flange

| No. of Pins | INSTALLATION | A | B | C | D | P.C.D. | REFERENCE | PART NUMBER |
|-------------|--------------|--------------|---------------|----------------|----------------|-------------|------------|-------------|
| 1 | CF 1.33 | 1.33 (34) | .30 (7.5) | 2.21 (56) | 1.73 (44) | — (—) | C15K22A1CU | 10599 |
| 2 | CF 1.33 | 1.33 (34) | .30 (7.5) | 1.77 (44.8) | 2.17 (55.2) | .32 (8) | C15K22A2CU | 10215 |
| 4 | CF 1.33 | 1.33 (34) | .30 (7.5) | 1.77 (44.8) | 2.17 (55.2) | .40 (10) | C15K22A4CU | 10214 |
| 1 | CF 2.75 | 2.75 (70) | .50 (12.7) | 2.21 (56) | 1.73 (44) | — (—) | C25K22A1CU | 12153 |
| 2 | CF 2.75 | 2.75 (70) | .50 (12.7) | 2.21 (56) | 1.73 (44) | .32 (8) | C25K22A2CU | 12181 |
| 4 | CF 2.75 | 2.75 (70) | .50 (12.7) | 2.21 (56) | 1.73 (44) | .40 (10) | C25K22A4CU | 10611 |

Accessories

| Description | REFERENCE | PART NUMBER |
|--------------------------------|-----------|-------------|
| .05 Socket Contact Vacuum Side | SVC15 | 10146 |

For more details, see Section 6.4

Introduction
Table of Contents
Glance
Coaxial
Multipin
Thermocouple
High Voltage & High Current
Isolator
Accessories
Custom-made products
Technical Data
Part number & Reference Index
Custom-made Application Sheet
Trademarks