

BNC-R Single Ended Grounded Shield Coaxial



THE NEW VALUE FRONTIER
KYOCERA

Section
1.1

Coaxial
BNC-R

Coaxial
BNC-R Single Ended Grounded Shield

Introduction
Table of Contents
Glance
Coaxial
Multipin
Thermocouple
High Voltage & High Current
Isolator
Accessories
Custom-made products
Technical Data
Part number & Reference Index
Custom-made Application Sheet
Trademarks

Dimensions in inches (mm)

NW / KF Flange

No. of Pins	INSTALLATION	A	B	C	D	REFERENCE	PART NUMBER
1	NW / KF 16	1.18 (30)	.24 (6)	.60 (15.3)	1.12 (28.5)	N16BR1	10319
1	NW / KF 25	1.57 (40)	.24 (6)	.60 (15.3)	1.12 (28.5)	N25BR1	10280
1	NW / KF 40	2.16 (55)	.24 (6)	.60 (15.3)	1.12 (28.5)	N40BR1	10298
2	NW / KF 40	2.16 (55)	.24 (6)	.60 (15.3)	1.12 (28.5)	N40BR2	10116
3	NW / KF 40	2.16 (55)	.24 (6)	.60 (15.3)	1.12 (28.5)	N40BR3	10297
4	NW / KF 40	2.16 (55)	.24 (6)	.60 (15.3)	1.12 (28.5)	N40BR4	10117

ConFlat® Flange

No. of Pins	INSTALLATION	A	B	C	D	REFERENCE	PART NUMBER
1	CF 1.33	1.33 (34)	.30 (7.5)	.62 (15.8)	1.10 (28)	C34BR1	10338
1	CF 2.75	2.75 (70)	.50 (12.7)	.62 (15.8)	1.10 (28)	C70BR1	10291
2	CF 2.75	2.75 (70)	.50 (12.7)	.62 (15.8)	1.10 (28)	C70BR2	10039
3	CF 2.75	2.75 (70)	.50 (12.7)	.62 (15.8)	1.10 (28)	C70BR3	10300
4	CF 2.75	2.75 (70)	.50 (12.7)	.62 (15.8)	1.10 (28)	C70BR4	10333

Accessories

Description	REFERENCE	PART NUMBER
BNC-R In-Vacuum Cable Assembly 19"/X	VCA500BR/X	11813
BNC-R In-Vacuum Cable Assembly 39"/X	VCA1000BR/X	11828
.094 Socket Contact Set Screw Vacuum Side	SVC24S	10152
BNC Air Side Plug	ASP-BNC	10017

For more details, see Section 6.1