

# SHV-R Single Ended Grounded Shield Coaxial



THE NEW VALUE FRONTIER  
**KYOCERA**

Section  
**1.2**

Coaxial  
**SHV-R**

Coaxial  
**SHV-R Single Ended Grounded Shield**

Dimensions in inches (mm)

## NW / KF Flange

No. of Pins	INSTALLATION	A	B	C	D	REFERENCE	PART NUMBER
1	NW / KF 16	1.18 (30)	.24 (6)	.49 (12.5)	1.30 (33)	N16SHR1	10430
1	NW / KF 25	1.58 (40)	.24 (6)	.49 (12.5)	1.30 (33)	N25SHR1	10431
1	NW / KF 40	2.16 (55)	.24 (6)	.49 (12.5)	1.30 (33)	N40SHR1	10197
2	NW / KF 40	2.16 (55)	.24 (6)	.49 (12.5)	1.30 (33)	N40SHR2	10228
3	NW / KF 40	2.16 (55)	.24 (6)	.49 (12.5)	1.30 (33)	N40SHR3	11178
4	NW / KF 40	2.16 (55)	.24 (6)	.49 (12.5)	1.30 (33)	N40SHR4	10235

## ConFlat® Flange

No. of Pins	INSTALLATION	A	B	C	D	REFERENCE	PART NUMBER
1	CF 1.33	1.33 (34)	.30 (7.5)	.51 (13)	1.28 (32.5)	C34SHR1	10301
1	CF 2.75	2.75 (70)	.50 (12.7)	.51 (13)	1.28 (32.5)	C70SHR1	10436
2	CF 2.75	2.75 (70)	.50 (12.7)	.51 (13)	1.28 (32.5)	C70SHR2	10049
3	CF 2.75	2.75 (70)	.50 (12.7)	.51 (13)	1.28 (32.5)	C70SHR3	10239
4	CF 2.75	2.75 (70)	.50 (12.7)	.51 (13)	1.28 (32.5)	C70SHR4	10050

## Accessories

Description	REFERENCE	PART NUMBER
SHV-R In-Vacuum Cable Assembly 19"/X	VCA500SHR/X	11814
SHV-R In-Vacuum Cable Assembly 39"/X	VCA1000SHR/X	11829
.062 Socket Contact Vacuum Side	SVC16	10147
SHV Air Side Plug	ASP-SHV	10002

For more details, see Section 6.1

Introduction  
Table of Contents  
Glance  
**Coaxial**  
Multipin  
Thermocouple  
High Voltage & High Current  
Isolator  
Accessories  
Custom-made products  
Technical Data  
Part number & Reference Index  
Custom-made Application Sheet  
Trademarks