

Special Hand Brushes



Special Hand Brushes

Filling	Rows	KL	KB	BL	H	Pack.	Art.-No.
ROKI® Brake Caliper Brushes with Two-Components		mm inch	mm inch	mm inch	mm inch		
1 STA straight 0.35 0.014"	2 x 12/13	225 9	12 1/2	90 3 1/2	22 7/8	10	182.401
STA crimped 0.30 0.012"	2 x 12/13	225 9	12 1/2	90 3 1/2	22 7/8	10	182.411
2 STA straight 0.35 0.014"	2 x 12/13	225 9	12 1/2	90 3 1/2	14/22 1/2/7/8	10	182.431*
3 ROF straight 0.35 0.014"	2 x 12/13	225 9	12 1/2	90 3 1/2	22 7/8	10	182.421
RO4 straight 0.35 0.014"	2 x 12/13	225 9	12/18 1/2/3/4	85 3 3/8	22 7/8	10	182.441
4 MES crimped 0.25 0.010"	2 x 12/13	225 9	12 1/2	90 3 1/2	22 7/8	10	182.451

Hand Brushes with Plastic Handles

5	STA straight 0.35 0.014"	2	285 11 1/4	20 3/4	130 5 1/8	25 1	10	185.121
	STA straight 0.35 0.014"	3	285 11 1/4	26 1	130 5 1/8	25 1	10	185.131
	STA straight 0.35 0.014"	4	285 11 1/4	31 1 1/4	130 5 1/8	25 1	10	185.141
	STA straight 0.35 0.014"	5	285 11 1/4	31 1 1/4	130 5 1/8	25 1	10	185.151
	ROF crimped 0.35 0.014"	2	285 11 1/4	20 3/4	130 5 1/8	25 1	10	185.421
	ROF crimped 0.35 0.014"	3	285 11 1/4	26 1	130 5 1/8	25 1	10	185.431
	ROF crimped 0.35 0.014"	4	285 11 1/4	31 1 1/4	130 5 1/8	25 1	10	185.441
	ROF crimped 0.35 0.014"	5	285 11 1/4	31 1 1/4	136 5 1/8	25 1	10	185.451
	MES straight 0.35 0.014"	2	285 11 1/4	20 3/4	130 5 1/8	25 1	10	185.621
	MES straight 0.35 0.014"	3	285 11 1/4	26 1	130 5 1/8	25 1	10	185.631
	MES straight 0.35 0.014"	4	285 11 1/4	31 1 1/4	130 5 1/8	25 1	10	185.641
	MES straight 0.35 0.014"	5	285 11 1/4	31 1 1/4	130 5 1/8	25 1	10	185.651

Hand Brushes with Two-Components Handles

6	ROF straight 0.35 0.014"	3	285 11 1/4	26 1	130 5 1/8	25 1	10	186.431
----------	----------------------------	---	--------------	--------	-------------	--------	----	----------------

* The brush has to the top a sloping filling and is therefore extra hard
 For the food industry

