


RENY/AJ

ガラス繊維強化ポリアミドMXD6 / 樹脂ジョイント
Glass-fiber-reinforced polyamideMXD6 / Plastics joint

→ P.56

RENY-BK/LC

ガラス繊維強化ポリアミドMXD6 / 六角穴付低頭ボルト
Glass-fiber-reinforced polyamideMXD6 / Hexagon socket low head cap bolt




品番 Product number		RENY-BK/LC-M○-L○							
M		M3	M4	M5	M6				
ピッチ / Pitch		0.5	0.7	0.8	1				
D × H		5.5 × 2	7 × 2.8	8.5 × 3.5	10 × 4				
B		2	2.5	3	4				
L	6	1,000	1,000	500	—				
	8	1,000	1,000	500	—				
	10	1,000	1,000	500	500				
	12	1,000	1,000	500	500				
	16	1,000	1,000	500	500				
	20	1,000	500	500	250				
	25	—	500	250	250				
	30	—	—	250	200				
40	—	—	—	100					

販売単位 Quantity

RENY-BK/LH

ガラス繊維強化ポリアミドMXD6 / ヘキサロビュラ穴付低頭ボルト
Glass-fiber-reinforced polyamideMXD6 / Hexalobular socket low head cap bolt




品番 Product number		RENY-BK/LH-M○-L○							
M		M3	M4	M5	M6				
ピッチ / Pitch		0.5	0.7	0.8	1				
D × H		5.5 × 2.4	7 × 3.1	8.5 × 3.65	10 × 4.4				
穴番号 / Hexalobular number		10	20	25	30				
L	6	1,000	1,000	500	—				
	8	1,000	1,000	500	—				
	10	1,000	1,000	500	500				
	12	1,000	1,000	500	500				
	16	1,000	1,000	500	500				
	20	1,000	500	500	250				
	25	—	500	250	250				
	30	—	—	250	200				
40	—	—	—	100					

販売単位 Quantity

RENY-BK/SH

ガラス繊維強化ポリアミドMXD6 / ヘキサロビュラ穴付極低頭ボルト
Glass-fiber-reinforced polyamideMXD6 / Hexalobular socket special low head cap bolt



品番 Product number		RENY-BK/SH-M○-L○							
M		M3	M4	M5	M6				
ピッチ / Pitch		0.5	0.7	0.8	1				
D × H		6 × 1.3	8 × 1.5	9 × 1.5	10 × 1.5				
穴番号 / Hexalobular number		8	10	15	20				
L	6	1,000	1,000	500	—				
	8	1,000	1,000	500	—				
	10	1,000	1,000	500	500				
	12	1,000	1,000	500	500				
	16	1,000	1,000	500	500				
	20	1,000	500	500	250				
	25	—	500	250	250				
	30	—	—	250	200				
40	—	—	—	100					

販売単位 Quantity

ORDER ▶ 品番・サイズ・販売単位にてご注文ください

RoHS compliant