


SLT/SLTS Hexalobular Socket Head Cap Screws with Low Profile



SUS Stainless steel Protrusion



● **Application**

Reducing the size of equipment and devices

● **Material/Finish**



	SLT-TZB	SLTS
Main Body	SAE1022 Trivalent Chromate Treatment	SUSXM7 (Equivalent to SUS304)
Strength Class	8.8	A2-50

● **Part number specification**

SLT - M5 - 20 - TZB



- Hexalobular socket*1 head cap screws with low head height.
- For space-saving of equipment/devices and applications with limited overhead space.
- Hexalobular socket shapes*1 are designed to withstand high tightening torque. → P.xxxx
- Install and remove with **SKX** Dedicated Wrench or **SKXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- Use the **SKX-N** hexalobular wrench for extremely limited access spaces for mounting and removing in tight spaces.

*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

SLT-TZB	SLTS	Common dimensions														Qty per pack							
Steel - Trivalent Chromate Treatment	Stainless steel	M (Coarse)		L										D1	L1	Applicable wrench	Hexalobular Socket No.	t	Mass (g)	Unit : mm			
Part Number	Part Number	Nominal of Thread	Pitch	4	5	6	8	10															
	SLTS-M2	M2	0.4	4	5	6	8	10									3.8	1.55	SKX-6	6	0.84	0.11 - 0.23	50
	SLTS-M2.5	M2.5	0.45	5	6	8	10	12									4.5	1.85	SKX-8	8	0.91	0.26 - 0.47	50
SLT-M3-TZB	SLTS-M3	M3	0.5			6	8	10	12	16							5.5	2.4	SKX-10	10	1.27	0.53 - 0.98	50
SLT-M4-TZB	SLTS-M4	M4	0.7			6	8	10	12	16	20						7	3.1	SKX-20	20	1.66	1.1 - 2.3	50
SLT-M5-TZB	SLTS-M5	M5	0.8			8	10	12	16	20	25						8.5	3.65	SKX-25	25	1.91	1.8 - 4.1	50
SLT-M6-TZB	SLTS-M6	M6	1			8	10	12	16	20	25	30					10	4.4	SKX-30	30	2.29	3.1 - 7.1	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● **Related Products**

SKX Hexalobular Wrench



SKXB Hexalobular Short Bit



SKX-N Hexalobular Wrench for Extremely Limited Access Spaces



SRD Magnet Screwdriver



Individual Sales → P.xxxx Cleanroom Wash & Packaging → P.xxxx Screw Length Adjustment → P.xxxx Vibration Resistant → P.xxxx Modification process for captive use → P.xxxx
Available / Add'l charge Available / Add'l charge Available / Add'l charge Available / Add'l charge Please feel free to contact us