

RoHS Compliant

ERON®

No.E-402

T-Slot Nuts



Material S45C **Heat Treatment** HRC30 ± 5 heat treatment

Surface Treatment Blackened

- Has specifications where the bolt cannot pass through in order to prevent damaging the T-slot by the bolt protruding.

Reference Pages

T-slot nut (SUS)



Specifications

Order No.	No.	Compatible T-slot Width	Screw Diameter (Coarse Thread)	A ± 0.3	B	C	D	E	Weight (g)		
113056	TNM1006	10	M6×1.0	9	14.3	6.4	12.7	22	23		
01108	TNM1008	10	M8×1.25	9	14.3	6.4	12.7	22	23		
113057	TNM1208	12	M8×1.25	11.5	17.5	6.4	12.7	22	28		
02571	TNM1210	12	M10×1.5	11.5	17.5	6.4	12.7	22	27		
02572	TNM1410	14	M10×1.5	13.5	22.2	8.5	15.8	29	55		
02581	TNM1412	14	M12×1.75	13.5	22.2	8.5	15.8	29	51		
02630	TNM1612	16	M12×1.75	15.3	25.4	8.5	15.8	29	63		
02631	TNM1614	16	M14×2	15.3	25.4	8.5	15.8	29	59		
113058	TNM1810	18	M10×1.5	17	28.6	11.1	19.1	32	105		
15817	TNM1812	18	M12×1.75	17	28.6	11.1	19.1	32	102		
02632	TNM1814	18	M14×2	17	28.6	11.1	19.1	32	96		
02633	TNM1816	18	M16×2	17	28.6	11.1	19.1	32	89		
02634	TNM2016	20	M16×2	19.5	31.8	11.9	19.1	32	108		
02635	TNM2018	20	M18×2.5	19.5	31.8	11.9	19.1	32	100		
25179	TNM2216	22	M16×2	21.5	36	14.2	25.4	38	193		
02636	TNM2218	22	M18×2.5	21.5	36	14.2	25.4	38	182		
02637	TNM2220	22	M20×2.5	21.5	36	14.2	25.4	38	171		
25551	TNM2416	24	M16×2	23.5	38.2	14.2	25.4	38	214		
02638	TNM2418	24	M18×2.5	23.5	38.2	14.2	25.4	38	203		
02639	TNM2420	24	M20×2.5	23.5	38.2	14.2	25.4	38	192		
02640	TNM2620	26	M20×2.5	24.9	41.3	15.8	25.4	45	263		
02641	TNM2622	26	M22×2.5	24.9	41.3	15.8	25.4	45	250		
32558	TNM2816	28	M16×2	26.5	41.3	17.5	28.6	51	378		
39331	TNM2820	28	M20×2.5	26.5	41.3	17.5	28.6	51	353		
02642	TNM2822	28	M22×2.5	26.5	41.3	17.5	28.6	51	338		
02643	TNM2824	28	M24×3	26.5	41.3	17.5	28.6	51	326		
03330	TNM3224	32	M24×3	31.3	47.6	19.1	31.8	54	450		
03331	TNM3227	32	M27×3	31.3	47.6	19.1	31.8	54	420		
03332	TNM3630	36	M30×3.5	35.5	50	22.2	44.5	64	750		
03333	TNM4236	42	M36×4	40	62	27	52	72	1150		

Base Elements

Clamp Units

Clamping Parts

Machine Vises

Drilling Vises

Vibration Isolation

Surface Plates and Measurement Instruments

Index