

# NAKANISHI'S EXCLUSIVE TOOLS

## Exclusive Tools of "IMPULSE"



Special tools for Nakanishi Micro-grinder "IMPULSE".  
Excellent for grinding or polishing flat surfaces, edges with Nakanishi's high-power air grinder.




90° ANGLE IMPULSE  
· NA90-230

60° ANGLE IMPULSE  
· NA45-230

### 5 pcs./pack Special Rubber Pad for Disk Abrasives




### 12 pcs./pack Cup Wheel



Grit	Grade Hardness	ø20	ø30
# 36	Standard	64830	64835
# 46	Hard	64831	64836
# 80	Standard	64832	64837
# 80	Hard	—	64838

### 5 pcs./pack Polishing Sander

• Abrasive Disk for high speed rotation is made from overlapping abrasive cloths.




Grit	
# 80	64842
# 120	64844
# 180	64846
# 240	64847
# 400	64849

• Convenient Assorted set for trial polishing  
All grain size (5 types x each 1 pc.)  
Total 5 pcs.-pack ..... 64850

### 10 pcs./pack Rubber Cup Wheel

• Rubber Cup Wheel with high elasticity for grinding & polishing.



Grit	Color	
# 60	Brown	64851
# 80	Red	64852
# 120	Blue	64853
# 180	Olive	64854
# 220	Green	64855
# 320	Brown	64856

• Convenient Assorted set for trial polishing  
All grain size (6 types x each 2 pcs.)  
Total 12 pcs.-pack ..... 64859

## Exclusive Tools of "FINE BELT SANDER"



FINE BELT SANDER E-max Evolution

### 30 pcs./pack Abrasive Belts

• High Quality Abrasive Belts are superior in grinding & durability.

For Grinding or Polishing of Metals (Length 300 mm)



Grit	W = 4 mm	W = 6 mm	W = 8 mm
# 80	64901	64911	• 64921
# 120	64902	64912	• 64922
# 180	64903	64913	• 64923
# 240	64904	64914	• 64924
# 320	64905	64915	• 64925
# 400	64906	64916	• 64926
# 600	—	—	• 64927
# 800	—	—	• 64928

• Assorted set for preliminary finishing (● Mark)  
Grain size (4 types x each 10 pcs.), W = 8 mm  
Total 40 pcs.-pack ..... 64931

• Assorted set for finishing (● Mark)  
Grain size (4 types x each 10 pcs.), W = 8 mm  
Total 40 pcs.-pack ..... 64932

For Woodwork (Length 300 mm)



Grit	8 mm Width
# 80	64941
# 120	64942
# 240	64943

• Assorted set for woodwork  
All grain size (3 types x each 10 pcs.)  
Total 30 pcs.-pack ..... 64955