

CC-GRIND-SOLID SG STEEL ★★☆☆

Materials that can be worked:
steel

Applications:
surface grinding, weld dressing, chamfering, deburring


Recommendations for use:

- For optimum results, use with a flat contact angle and the SFS CC-GRIND clamping flange set.
- Only use the face of the disc, not suitable for peripheral grinding.

Ordering notes:

- Please order clamping flange set SFS separately.

PFERDVALUE:



D [mm]	EAN 4007220	H [mm]	Max. RPM		Description
SOLID					
100	919682	16.0	15,300	10	CC-GRIND-SOLID 100 SG STEEL/16,0
115	887059	22.23	13,300	10	CC-GRIND-SOLID 115 SG STEEL
125	887073	22.23	12,200	10	CC-GRIND-SOLID 125 SG STEEL
150	952894	22.23	10,200	10	CC-GRIND-SOLID 150 SG STEEL
180	887080	22.23	8,500	10	CC-GRIND-SOLID 180 SG STEEL

CC-GRIND-SOLID SG INOX ★★☆☆

Materials that can be worked:
stainless steel (INOX)

Applications:
weld dressing, chamfering, deburring


Recommendations for use:

- For optimum results, use with a flat contact angle and the SFS CC-GRIND clamping flange set.
- Only use the face of the disc, not suitable for peripheral grinding.

Ordering notes:

- Please order clamping flange set SFS separately.

PFERDVALUE:



D [mm]	EAN 4007220	H [mm]	Max. RPM		Description
SOLID					
115	900895	22.23	13,300	10	CC-GRIND-SOLID 115 SG INOX
125	900901	22.23	12,200	10	CC-GRIND-SOLID 125 SG INOX
180	900918	22.23	8,500	10	CC-GRIND-SOLID 180 SG INOX

CC-GRIND clamping flange set

The CC-GRIND clamping flange set optimally aligns the CC-GRIND-SOLID and -FLEX in the angle grinder protective guard. This allows a very flat contact angle and thus maximum efficiency.

The black backing pad is placed on the original mounting flange of the angle grinder. The silver flange nut replaces the original flange nut.



Suitable for angle grinders	EAN 4007220		Description
Metric			
100 mm, M10 spindle	932209	1	SFS CC-GRIND 100 M10
115 / 125 mm, M14 spindle	887578	1	SFS CC-GRIND 115/125 M14
150 / 180 mm, M14 spindle	887585	1	SFS CC-GRIND 150/180 M14
Imperial			
115 / 125 mm, 5/8"-11 spindle	887592	1	SFS CC-GRIND 115/125 5/8"
150 / 180 mm, 5/8"-11 spindle	887608	1	SFS CC-GRIND 150/180 5/8"

