

# SOLID BIT 商品一覧

## ■方形バイト (ミリ)

寸 法	材質・在庫				W・H公差
	W=H	L	SM	SPM	
4	50	○	○		0 } -0.18
	63	○	○		
	80	○	○		
5	50	○	○		
	63	○	○		
	80	○	○		
	100	○	○		
	160	○	○		
6	63	○	○		
	80	○	○		
	100	○	○		
	125	○	○		
7	63	○	○		
	80	○	○		
	100	○	○		
	160	○	○		
8	63	○	○		
	80	○	○		
	100	○	○		
	125	○	○		
	160	○	○		
10	63	○	○		
	80	○	○		
	100	○	○		
	125	○	○		
	160	○	○		
12	63	○	○		
	80	○	○		
	100	○	○		
	125	○	○		
	160	○	○		
13	100	○	○		
	100	○	○		
	125	○	○		
14	160	○	○		
	200	○	○		
	200	○	○		
16	100	○	○		
	125	○	○		
	160	○	○		
18	200	○	○		
	200	○	○		
20	160	○	○		
	200	○	○		
25	160	○	○		
	200	○	○		

## ■方形バイト (インチ)

呼 称	size (mm)		材質・在庫			W・H公差
	W=H	L	SM	SPM	W・H公差	
3/16	2	4.76	50	○	○	0 } -0.18
	2 1/2		63	○	○	
	4		100	○	○	
1/4	2	6.35	50	○	○	
	2 1/2		63	○	○	
	3		76	○	○	
	4		101	○	○	
	5		127	○	○	
	6		152	○	○	
5/16	2 1/2	7.98	63	○	○	
	3		76	○	○	
	4		101	○	○	
	5		127	○	○	
	6		152	○	○	
3/8	2 1/2	9.52	63	○	○	
	3		76	○	○	
	4		101	○	○	
	5		127	○	○	
	6		152	○	○	
7/16	3 1/2	11.11	88	○	○	
	4		101	○	○	
	4 1/2		115	○	○	
1/2	3	12.70	76	○	○	
	4		101	○	○	
	5		127	○	○	
	6		152	○	○	
5/8	4 1/2	15.87	115	○	○	
	5		127	○	○	
	6		152	○	○	
	8		203	○	○	
3/4	5	19.05	127	○	○	
	6		152	○	○	
	8		203	○	○	
7/8	6	22.22	152	○	○	
	7		177	○	○	
1	7	25.40	177	○	○	
	8		203	○	○	

インチ・ミリメートル換算表

インチ(分数)	(分)	ミリメートル
1/8	1分	3.175
3/16		4.763
1/4	2分	6.350
5/16		7.938
3/8	3分	9.525
7/16		11.113
1/2	4分	12.700
5/8	5分	15.875
3/4	6分	19.050
7/8	7分	22.225
1	8分	25.400

白抜き	1本単位
■	2本単位
■	3本単位
■	5本単位
■	10本単位

※ロット数以外の御発注の場合は割増となります。