

# Recoil Kits/Tools Unified

Thread Size/Pitch UNF	Kits	Installation Tools	Pre- Winder	Production Insertion Tools			Electric Mandrels	Tangbreak Tools	Extraction Tool	Gauges	
				Mandrel	Light - Weight	Non - Captive				3BCLOSE	2BMED
*#3 - 56	34538	50069-17	54531					59070M	50002	64533	64532
*#4 - 48	34548	50077-17	54541		54542U			59080M	50002	64543	64542
*#6 - 40	34568	50095-17	54561		54562U			59100M	50002	64563	64562
*#8 - 36	34588	50125-14	54581		54582U			59130M	50002	64583	64582
*#10 - 32	34608	50156-11	54601		54602U		54607B	59160M	50002	64603	64602
*#12 - 28	34628	50156-10						59160M	50002		
*1/4 - 28	34048	50188-10	54041		54042U		54047B	59190M	50002	64043	64042
*5/16 - 24	34058	50250-8	54051		54052U		54057B	59250M	50002	64053	64052
*3/8 - 24	34068	50313-6	54061		54062U		54067B	59280M	50002	64063	64062
*7/16 - 20	34078	50344-4	54071		54072U		54077B	59310M	50003	64073	64072
*1/2 - 20	34088	50375-3	54081		54082U		54087B	59380M	50003	64083	64082
9/16 - 18	34098	50438-0				54091			50003	64093	64092
5/8 - 18	34108	50500-0				54101			50003	64103	64102
3/4 - 16	34128	50591-0				54121			50003	64123	64122
7/8 - 14	34140	50688				54141			50003	64143	64142
1" - 12	34160	50750				54161			50003	64163	64162
1" - 14	34160-14	50750				54171			50003	64163-14	64162-14
1 1/8 - 12	34180	51000				54181			50004	64183	64182
1 1/4 - 12	34200	51063							50004	64203	64202
1 3/8 - 12	34220	51125							50004	64223	64222
1 1/2 - 12	34240	51250							50004	64243	64242
<b>BA</b>											
	<b>Kits</b>	<b>Tools</b>									
*0BA	30508	50188-5						59190M	50002		60502
*2BA	30528	50140-9						59140M	50002		60522
*4BA	30548	50095-15						59100M	50002		60542
*6BA	30568	50077-17						59070M	50002		60562
<b>BSC</b>											
*5/16 - 26	36508	50250-4						59250M	50002		66502
*3/8 - 26	36608	50313-5						59310M	50002		66602
*7/16 - 26	36708	50344-4						59340M	50003		66702
*1/2 - 26	36808	50375-1						59380M	50003		66802
<b>BSF</b>											
*3/16 - 32	30038	50156-9						59160M	50002		60032
*1/4 - 26	30048	50188-5						59190M	50002		60042
*5/16 - 22	30058	50250-5						59250M	50002		60052
*3/8 - 20	30068	50281-5						59280M	50002		60062
*7/16 - 18	30078	50344-4						59340M	50003		60072
*1/2 - 16	30088	50375-1						59380M	50003		60082
9/16 - 16	30098	50438-0							50003		60092
5/8 - 14	30108	50500-0							50003		60102
3/4 - 12	30128	50591-0							50003		60122
7/8 - 11	30140	50688							50003		60142
1" - 10	30160	50750							50003		60162
1 1/4 - 9	30200*	51000									60202

\* Drill and magnetic tangbreak tool included