

Color Variation Selectable in 18 types listed below

Color						
Color code	Black / Pink [B][P]	Black / Yellow [B][Y]	Black / Green [B][G]	Black / Navy [B][N]	Black / Light gray [B][L]	Black / Black [B][B]
Color						
Color code	Light gray / Pink [G][P]	Light gray / Yellow [G][Y]	Light gray / Green [G][G]	Light gray / Navy [G][N]	Light gray / Light gray [G][L]	Light gray / Black [G][B]
Color						
Color code	Off-white / Pink [W][P]	Off-white / Yellow [W][Y]	Off-white / Green [W][G]	Off-white / Navy [W][N]	Off-white / Light gray [W][L]	Off-white / Black [W][B]

• Note: The plastic enclosure material is different by color. Black and Light gray are ABS UL94HB, Off-white is ABS UL94V-0.

ABS (UL94HB)

Part no. / Dimensions

• Please suffix color code listed above at the ending of part number □□ when ordering TWS series.

Part no.	W	H	D	Plastic case material
TWS 7-3-13□□	71(65)	32(25.8)	136(130)	ABS(UL94HB)
TWS 7-5-13□□	71(65)	56(50.1)	136(130)	ABS(UL94HB)
TWS 9-4-17□□	91.5(85.5)	41.5(35.5)	176(170)	ABS(UL94HB)
TWS 9-6-17□□	91.5(85.5)	66.5(60.5)	176(170)	ABS(UL94HB)
TWS11-5-22□□	116(110)	51.5(45.3)	226(220)	ABS(UL94HB)
TWS11-8-22□□	116(110)	81.5(75.3)	226(220)	ABS(UL94HB)
TWS13-3-13□□	131(125)	31(25)	131(125)	ABS(UL94HB)
TWS13-5-13□□	131(125)	51(45)	131(125)	ABS(UL94HB)
TWS13-3-18□□	131(125)	31(25)	181(175)	ABS(UL94HB)
TWS13-5-18□□	131(125)	51(45)	181(175)	ABS(UL94HB)
TWS13-7-18□□	131(125)	71(65)	181(175)	ABS(UL94HB)

• () dimension = Dimension of inner case.

ABS (UL94V-0)

Part no. / Dimensions

• Please suffix color code listed above at the ending of part number W□ when ordering TWS series.

Part no.	W	H	D	Plastic case material
TWS 7-3-13W□	71(65)	32(25.8)	136(130)	ABS(UL94V-0)
TWS 7-5-13W□	71(65)	56(50.1)	136(130)	ABS(UL94V-0)
TWS 9-4-17W□	91.5(85.5)	41.5(35.5)	176(170)	ABS(UL94V-0)
TWS 9-6-17W□	91.5(85.5)	66.5(60.5)	176(170)	ABS(UL94V-0)
TWS11-5-22W□	116(110)	51.5(45.3)	226(220)	ABS(UL94V-0)
TWS11-8-22W□	116(110)	81.5(75.3)	226(220)	ABS(UL94V-0)
TWS13-3-13W□	131(125)	31(25)	131(125)	ABS(UL94V-0)
TWS13-5-13W□	131(125)	51(45)	131(125)	ABS(UL94V-0)
TWS13-3-18W□	131(125)	31(25)	181(175)	ABS(UL94V-0)
TWS13-5-18W□	131(125)	51(45)	181(175)	ABS(UL94V-0)
TWS13-7-18W□	131(125)	71(65)	181(175)	ABS(UL94V-0)

• () dimension = Dimension of inner case.