

Prices displayed include 8% tax.

For Die Handle, see p. 1-424 to 425

YAMAWA
Think threads with **YAMAWA**
Stock 1,368 Items

Solid Die for Unified Thread (Coarse)



D-8-32UNC-20

- Features** •Solid die with improved runout accuracy. The use of high-speed steel tool (HSS) ensures stable machining.
- Use** •Work Material: Iron, Light Metal. •For external thread machining.
- Specs** •Machining Thread: Unified Thread
- Materials** •High Speed Steel (HSS)
- Origin** •Japan

SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Jul, 2016) YAMAWA MANUFACTURING Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)
775-9991	D-4-40UNC-20	¥5,670	¥7,000	No.4	40	20	7
776-0019	D-6-32UNC-20	¥5,670	¥7,000	No.6	32	20	7
776-0027	D-8-32UNC-20	¥5,670	¥7,000	No.8	32	20	7
776-0035	D-1/4-20UNC-20	¥5,670	¥7,000	UNC1/4	20	20	7
776-0043	D-1/2-13UNC-38	¥9,153	¥11,300	UNC1/2	13	38	13

Contact us:0120-800-418 <http://www.yamawa.com/jp/>

YAMAWA
Think threads with **YAMAWA**
Stock 1,368 Items

Solid Die for Unified Thread (Fine)



D-3/8-24UNF-38

- Features** •Solid die with improved runout accuracy. The use of high-speed steel tool (HSS) ensures stable machining.
- Use** •Work Material: Iron, Light Metal. •For external thread machining.
- Specs** •Machining Thread: Unified Thread
- Materials** •High Speed Steel (HSS)
- Origin** •Japan

SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Jul, 2016) YAMAWA MANUFACTURING Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)
776-0051	D-10-32UNF-20	¥5,670	¥7,000	No.10	32	20	7
776-0060	D-1/4-28UNF-20	¥5,670	¥7,000	UNF1/4	28	20	7
776-0078	D-3/8-24UNF-38	¥9,153	¥11,300	UNF3/8	24	38	13
776-0086	D-7/16-20UNF-38	¥9,153	¥11,300	UNF7/16	20	38	13
776-0094	D-1/2-20UNF-38	¥9,153	¥11,300	UNF1/2	20	38	13
776-0108	D-9/16-18UNF-38	¥9,153	¥11,300	UNF9/16	18	38	13

Contact us:0120-800-418 <http://www.yamawa.com/jp/>

YAMAWA
Think threads with **YAMAWA**
Stock 1,368 Items

Solid Die for Whitworth Thread



D-1/2W12-38

- Features** •Solid die with improved runout accuracy. The use of high-speed steel tool (HSS) ensures stable machining.
- Use** •Work Material: Iron, Light Metal. •For external thread machining.
- Specs** •Machining Thread: Whitworth Thread
- Materials** •High Speed Steel (HSS)
- Origin** •Japan

Order Unit: 1 Piece

(Price revision date: Jul, 2016) YAMAWA MANUFACTURING Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)	SPQ (piece)
775-9924	D-1/8W40-20	¥5,670	¥7,000	W1/8	40	20	7	1
775-9932	D-5/32W32-20	¥5,670	¥7,000	W5/32	32	20	7	1
775-9941	D-3/16W24-20	¥5,670	¥7,000	W3/16	24	20	7	1
775-9959	D-1/4W20-20	¥5,670	¥7,000	W1/4	20	20	7	1
775-9967	D-3/8W16-38	¥9,153	¥11,300	W3/8	16	38	13	1
775-9975	D-1/2W12-38	¥9,153	¥11,300	W1/2	12	38	13	1
775-9983	D-5/8W11-38	¥9,153	¥11,300	W5/8	11	38	13	1

Contact us:0120-800-418 <http://www.yamawa.com/jp/>


TRUSCO
Stock 38,650 Items

Round Adjustable Taper Pipe Die (PT thread)



TKD Series

- Features** •Adjustable screw allows you to adjust the dimension. •Can also be used when repairing ridge.
- Use** •Work Material: Low Carbon Steel •For external thread machining.
- Specs** •Machining Thread: Taper Thread for Pipe PT and R
- Materials** •Low-Alloy Steel (SKS2) **Origin** •Japan



Warning •Cannot be used for stainless steel screws.

SPQ: 1 Piece

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nominal Dimension	Number of Ridges	Outer Diameter (mm)	Thickness (mm)	Length to standard diameter (mm)
480-6522	TKD-38PT1/8-28	¥5,176	¥6,390	1/8	28	38	14	7.0
480-6514	TKD-38PT1/4-19	¥5,176	¥6,390	1/4	19	38	14	7.0
480-6611	TKD-50PT3/8-19	¥6,901	¥8,520	3/8	19	50	16	8.0
480-6590	TKD-50PT1/2-14	¥6,901	¥8,520	1/2	14	50	16	8.0
480-6603	TKD-50PT3/4-14	¥6,901	¥8,520	3/4	14	50	16	8.0
480-6646	TKD-63PT1-11	¥19,967	¥24,650	1	11	63	19	9.5
858-7624	TKD-75PT11/2-11	¥38,718	¥47,800	11/2	11	75	25	12.5
858-7625	TKD-75PT11/4-11	¥38,718	¥47,800	11/4	11	75	25	12.5

Contact us:0120-509-849 <http://www.orange-book.com/>

Spiral Fluted Taps

Point Taps

Roll Taps

Hand Taps

Hexagonal Shank Tapping Drills

Tap Holders

Taps for Pipe

Thread Mills for Machining Center

Dies

Thread Repair Tools

Tap and Bolt Burr Removing Tools

Screw

For other cutting tools, see p. 1-805 to 1006