

Low Head Machine Screws/Screw Checkers

Stock 792 Items

2-453

Screws • Bolts • Nuts

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

Ultra Low Head Machine Screw (steel)

RoHS


Com Drawing



TFSC Type



- Features**
- Since the height of the head is thin, the mounting surface can be flat.
 - Suitable for places where countersinking can not be performed, or where thickness becomes an obstacle.
- Specs**
- Tensile Strength Rank: Equivalent to A.8
- Materials**
- Carbon steel for cold forging (SWRCH12A)
- Origin**
- Japan
- Surface Treatment: Trivalent Chromate**



Basic Dimension (unit: mm)			
Nominal Designation of Thread (d)	Cross Recess Number	Head Outer Diameter dk	Head Thickness k
M3 x 0.5	1	6.0	0.8
M4 x 0.7	2	8.0	0.9
M5 x 0.8	2	9.0	1.0

Order Unit: 1 Bag TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x L	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
819-5315	TFSC-0306	¥602	¥650	M3 x 6	38	10	20.4
819-5316	TFSC-0308	¥602	¥650	M3 x 8	36	10	21.1
819-5317	TFSC-0310	¥602	¥650	M3 x 10	36	10	22.4
819-5318	TFSC-0312	¥602	¥650	M3 x 12	34	10	23.5
819-5319	TFSC-0406	¥602	¥650	M4 x 6	26	10	31.2
819-5320	TFSC-0408	¥602	¥650	M4 x 8	24	10	29.5
819-5321	TFSC-0410	¥602	¥650	M4 x 10	22	10	27.3

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x L	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
819-5322	TFSC-0416	¥602	¥650	M4 x 16	18	10	27.3
819-5323	TFSC-0420	¥602	¥650	M4 x 20	14	10	25.4
819-5324	TFSC-0430	¥602	¥650	M4 x 30	10	10	25.0
819-5325	TFSC-0510	¥602	¥650	M5 x 10	8	10	18.8
819-5326	TFSC-0515	¥602	¥650	M5 x 15	8	10	22.7
819-5327	TFSC-0520	¥602	¥650	M5 x 20	6	10	20.5
819-5328	TFSC-0530	¥602	¥650	M5 x 30	6	10	25.4

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Ultra Low Head Machine Screw (stainless steel)

RoHS


Com Drawing



TFSS Type



- Features**
- Since the height of the head is thin, the mounting surface can be flat.
 - Suitable for places where countersinking can not be performed, or where thickness becomes an obstacle.
- Specs**
- Tensile Strength Rank: Equivalent to A2-50
- Materials**
- Stainless Steel (SUS-XM7)
- Origin**
- Japan



Basic Dimension (unit: mm)			
Nominal Designation of Thread (d)	Cross Recess Number	Head Outer Diameter dk	Head Thickness k
M3 x 0.5	1	6.0	0.8
M4 x 0.7	2	8.0	0.9
M5 x 0.8	2	9.0	1.0

Order Unit: 1 Bag TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x L	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
819-5329	TFSS-0306	¥741	¥800	M3 x 6	18	10	12.4
819-5330	TFSS-0308	¥741	¥800	M3 x 8	18	10	12.8
819-5331	TFSS-0310	¥741	¥800	M3 x 10	16	10	12.7
819-5332	TFSS-0312	¥741	¥800	M3 x 12	16	10	13.3
819-5333	TFSS-0406	¥741	¥800	M4 x 6	14	10	19.5
819-5334	TFSS-0408	¥741	¥800	M4 x 8	14	10	19.7
819-5335	TFSS-0410	¥741	¥800	M4 x 10	12	10	20.2

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x L	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
819-6052	TFSS-0415	¥741	¥800	M4 x 15	10	10	22.4
819-5337	TFSS-0420	¥741	¥800	M4 x 20	10	10	21.8
819-5338	TFSS-0430	¥741	¥800	M4 x 30	8	10	20.1
819-5339	TFSS-0510	¥741	¥800	M5 x 10	10	10	30.1
819-5340	TFSS-0515	¥741	¥800	M5 x 15	8	10	31.9
819-5341	TFSS-0520	¥741	¥800	M5 x 20	6	10	22.8
819-5342	TFSS-0530	¥741	¥800	M5 x 30	6	10	23.4

Contact us: 0120-509-849 <http://www.orange-book.com/>

DAIDOHANT **Stock 357 Items**

Screw Checker

- Features**
- Possible to distinguish with more than 30 kinds of screws.
- Materials**
- Aluminum
 - Surface Finish: Alumite
- Origin**
- Japan



00092600 (for external threads)



Example

For external threads Use • To distinguish the external thread.

Order Unit: 1 Piece DAIDOHANT Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Comments	SPQ (piece)	Weight (kg)
418-4491	00092600	¥35,254	-	For bolts, machine screws	1	1.23



00092601 (for internal threads)

For internal threads Use • To distinguish internal threads.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Comments	SPQ (piece)	Weight (kg)
418-4505	00092601	¥35,254	-	For nuts, washers	1	1.32

Contact us: 06-6821-3037 <http://www.daidohant.com/>