

The number next to the logo mark indicates items in stock for each brand.

**TRUSCO** Stock **38,650** Items

## Round nail (steel)

**UKN Type**

**Features**

- Has a rust preventive effect by plating treatment.
- Suitable for wood.

**Materials**

- Steel
- **Surface Treatment: Unichrome**

**Origin**

- China

**TRUSCO** Stock **38,650** Items

## Round Nail (stainless steel)

**ST Type**

**Features**

- Excellent corrosion resistance, rust is hard to happen.
- Suitable for mounting aluminum sash, aluminum plate, roof tile attachment and duckboard nailing.

**Materials**

- Stainless Steel (SUS304)

**Origin**

- China

Order Unit: 1 Bag (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x Total Length	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
510-5862	UKN1625	¥444	¥480	1.70 x 25	300	10	140
510-5871	UKN1532	¥444	¥480	1.90 x 32	180	10	140
510-5889	UKN1438	¥444	¥480	2.15 x 38	120	10	140
510-5897	UKN1345	¥444	¥480	2.45 x 45	90	10	160
510-5901	UKN1250	¥444	¥480	2.75 x 50	60	10	160
510-5919	UKN1165	¥444	¥480	3.05 x 65	40	10	160
510-5927	UKN1075	¥444	¥480	3.40 x 75	28	10	170
510-5935	UKN990	¥444	¥480	3.75 x 90	20	10	170
510-5943	UKN8100	¥444	¥480	4.20 x 100	15	10	170

Contact us:0120-509-849 <http://www.orange-book.com/>

Order Unit: 1 Bag (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x Total Length	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
510-6141	ST1625F	¥454	¥490	1.70 x 25	120	10	60
510-6150	ST1532F	¥454	¥490	1.90 x 32	90	10	60
510-6168	ST1438F	¥454	¥490	2.15 x 38	54	10	60
510-6176	ST1345F	¥454	¥490	2.45 x 45	34	10	60
510-6184	ST1250F	¥454	¥490	2.75 x 50	25	10	60
510-6192	ST1165F	¥454	¥490	3.05 x 65	15	10	60
510-6206	ST1075F	¥454	¥490	3.40 x 75	10	10	60
510-6214	ST990F	¥454	¥490	3.75 x 90	7	10	60
511-5906	ST8100F	¥454	¥490	4.20 x 100	5	10	60

Contact us:0120-509-849 <http://www.orange-book.com/>

**TRUSCO** Stock **38,650** Items

## Screw Nail (steel)

**EGDS Type**

**Features**

- The retention force is strong since it is processed in the screw shape to the full length.
- Suitable for mounting pallets, weight packaging materials, flexible boards, wooden building construction, other vibration parts, etc.

**Materials**

- Steel
- **Surface Treatment: Unichrome**

**Origin**

- China

**TRUSCO** Stock **38,650** Items

## Screw Nail (stainless steel)

**STDS Type**

**Features**

- Since it is the screw shape processed, the retention force is strong.
- Suitable for installation of fire walls, fences, board base ceilings, plywood boards and the like.

**Materials**

- Stainless Steel (SUS304)

**Origin**

- China

Order Unit: 1 Bag (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x Total Length	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
510-5951	EGDS1625	¥444	¥480	1.90 x 25	210	10	100
510-5960	EGDS1532	¥444	¥480	2.10 x 32	130	10	100
510-5978	EGDS1438	¥444	¥480	2.40 x 38	85	10	100
510-5986	EGDS1345	¥444	¥480	2.70 x 45	70	10	130
510-5994	EGDS1250	¥444	¥480	3.10 x 50	50	10	130
510-6001	EGDS1165	¥444	¥480	3.45 x 65	30	10	130
510-6010	EGDS1075	¥444	¥480	3.75 x 75	24	10	140
510-6028	EGDS990	¥444	¥480	4.10 x 90	17	10	140
510-6036	EGDS8100	¥444	¥480	4.50 x 100	12	10	140

Contact us:0120-509-849 <http://www.orange-book.com/>

Order Unit: 1 Bag (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x Total Length	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
510-6231	STDS1625F	¥454	¥490	1.90 x 25	110	10	55
510-6249	STDS1532F	¥454	¥490	2.00 x 32	80	10	55
510-6257	STDS1438F	¥454	¥490	2.30 x 38	50	10	55
510-6265	STDS1345F	¥454	¥490	2.80 x 45	30	10	55
510-6273	STDS1250F	¥454	¥490	3.20 x 50	23	10	55
510-6281	STDS1165F	¥454	¥490	3.45 x 65	15	10	55
510-6290	STDS1075F	¥454	¥490	3.80 x 75	10	10	55
510-6303	STDS990F	¥454	¥490	4.15 x 90	7	10	55
510-6311	STDS8100F	¥454	¥490	4.70 x 100	5	10	55

Contact us:0120-509-849 <http://www.orange-book.com/>

**TRUSCO** Stock **38,650** Items

## Concrete Nail (steel)

**CK Type**

**Features**

- Heat treatment is given.
- Suitable for mounting pipes, concrete, blocks, lightweight section steel, cheek wood, iron plates, electric Equipment, sashes, etc.

**Materials**

- Steel
- **Surface Treatment: Unichrome**

**Origin**

- China

**TRUSCO** Stock **38,650** Items

**RoHS**

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Dimension (mm) d x Total Length	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
510-6044	CK1225HG	¥417	¥450	2.77 x 25	65	10	90
510-6052	CK1238HG	¥417	¥450	2.77 x 38	45	10	90
510-6061	CK1250HG	¥417	¥450	2.77 x 50	35	10	90
510-6087	CK1065HG	¥417	¥450	3.70 x 65	17	10	100
510-6095	CK1075HG	¥417	¥450	3.70 x 75	15	10	100
510-6109	CK925HG	¥417	¥450	3.98 x 25	35	10	100
510-6117	CK938HG	¥417	¥450	3.98 x 38	23	10	100
510-6125	CK950HG	¥417	¥450	3.98 x 50	22	10	120
510-6133	CK865HG	¥417	¥450	4.46 x 65	13	10	120

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>