

# Thimbles

For wire ropes, see p. 2-907 to 911

The number next to the logo mark indicates items in stock for each brand.

Hardware

TRUSCO



Stock 38,650 Items

## "Light Thimble"



- Features** • Use it as a wire course to process the terminal.  
**Use** • Prevention of wire wear when using wire rope tip processed with eye splice.  
**Materials** • **Stainless Steel (SUS304)**  
**Origin** • Taiwan



TRS-6

Example



Order Unit: 1 Bag

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Applicable Rope Diameter (mm)	D (mm)	L (mm)	A (mm)	B (mm)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
275-4207	TRS-2	¥361	¥390	2	8	17	2.5	4	2	20	2
275-4215	TRS-3	¥389	¥420	3	9	17	3.5	5	2	20	4
275-4223	TRS-4	¥342	¥370	4	10	19	4.5	6	2	20	6
275-4231	TRS-5	¥352	¥380	5	13	21	5.5	7	2	20	8
275-4240	TRS-6	¥407	¥440	6	15	25	7.0	9	2	20	14
275-4258	TRS-8	¥278	¥300	8	20	35	9.0	12	1	20	19
275-4266	TRS-10	¥269	¥290	10	25	42	12.0	15	1	20	27

Contact us:0120-509-849 <http://www.orange-book.com/>


Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches



Handles

TRUSCO



Stock 38,650 Items

## Thimble



- Features** • Use it as a wire course to process the terminal.  
**Use** • Prevention of wire wear when using wire rope tip processed with eye splice.  
**Materials** • **Steel**  
**Origin** • China



TSP-012

Example



Item No.	Surface Treatment
TSP-006	Unichrome Plated
TSP-008	Hot dip galvanizing
TSP-010	Hot dip galvanizing
TSP-012	Hot dip galvanizing

Order Unit: 1 Piece


TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Applicable Rope Diameter (mm)	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	SPQ (piece)	Weight (g)
275-7559	TSP-006	¥194	¥210	6	31	18	45	28	12	7	50	22
275-7567	TSP-008	¥222	¥240	8	40	24	59	38	15	10	50	40
275-7575	TSP-010	¥241	¥260	10	48	28	70	45	17	12	50	72
275-7583	TSP-012	¥269	¥290	12	53	32	76	51	21	14	50	143

Contact us:0120-509-849 <http://www.orange-book.com/>

Joint Fittings

Steel Wires



Wire Nets

TRUSCO



Stock 38,650 Items

## Forged A Type Thimble



- Features** • It prevents direct loading to the eye part of a wire rope and deformation/wear.  
 • It keeps the wire rope life longer.  
**Use** • For a wire course/protective bracket when applying eye processing at the wire rope tip.  
**Specs** • Compliant for the previous JIS B2802 standard  
**Materials** • **Iron (hot dip galvanizing)**  
**Origin** • China



TAT series

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Applicable Rope Diameter (mm)	L (mm)	B (mm)	D1 (mm)	SPQ (piece)	Weight (g)
759-2531	TAT-06	¥166	¥180	6	36	8	16	100	20
759-2540	TAT-08	¥231	¥250	8	48	10	22	100	40
759-2558	TAT-09	¥249	¥270	9	51	11	25	100	50
759-2485	TAT-010	¥324	¥350	10	58	13	28	50	60
759-2493	TAT-012	¥370	¥400	12	68	15	34	50	90
759-2507	TAT-014	¥435	¥470	14	78	17	38	50	140
759-2515	TAT-016	¥565	¥610	16	92	20	44	40	190
759-2523	TAT-018	¥648	¥700	18	100	22	48	30	270

Contact us:0120-509-849 <http://www.orange-book.com/>

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers

