


Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

## Ring Catch "Quick Catch"



TQC-5 (with ring)



- Features**
- Since it is a slide type using spring force, not a screw type, it is resistant to vibration and workability is improved.
  - The ring part is knurled.
- Use**
- For a connecting/hanging brackets for chains, ropes, wire, etc.
- Specs**
- Slide type
- Materials**
- Stainless Steel (SUS304)
- Origin**
- China

Order Unit: 1 Piece (Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	B1 (mm)	B2 (mm)	S (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
300-8541	TQC-3	¥ 573	¥ 620	3	36	9.0	7.5	5.0	0.05	20	7
300-8550	TQC-4	¥ 658	¥ 710	4	48	13.0	12.0	6.5	0.10	20	15
300-8568	TQC-5	¥ 796	¥ 860	5	60	15.0	14.0	8.0	0.15	20	25
300-8576	TQC-6	¥ 1,027	¥ 1,110	6	70	18.5	17.0	9.0	0.29	20	46
300-8584	TQC-8	¥ 1,527	¥ 1,650	8	93	26.0	24.0	13.0	0.39	20	100


Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Ring Catch "Open Hook P Type"



TOFP-5 (with ring)



- Features**
- Since it is the outward opening structure with a ring, it does not accidentally open.
- Use**
- Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
- Materials**
- Stainless Steel (SUS304)
- Origin**
- China

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W1 (mm)	W2 (mm)	S (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
380-3767	TOFP-5	¥ 907	¥ 980	5	58	14.5	16	15	0.69	20	26
380-3775	TOFP-6	¥ 1,083	¥ 1,170	6	66	15.5	18	15	0.98	20	41
380-3783	TOFP-8	¥ 1,555	¥ 1,680	8	74	20.0	22	24	1.47	20	80
380-3759	TOFP-10	¥ 2,102	¥ 2,270	10	91	26.0	28	27	1.96	10	152

Contact us: 0120-509-849 <http://www.orange-book.com/>


TRUSCO **Stock 38,650 Items**

## Ring Catch "Carabiner Jr."



TKJR-1 (no ring)

TKJR-2 (with ring)



- Features**
- A spring hook.
  - The opening part returns with the force of the mechanical spring.
- Use**
- As joint brackets, for attaching to edges such as chains, etc.
- Materials**
- Stainless Steel (SUS304)
- Origin**
- China

**Warning**  
• It cannot be used as a safety belt.

Order Unit: 1 Piece (Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	D (mm)	L (mm)	W (mm)	S (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
409-9737	TKJR-1	¥ 2,333	¥ 2,520	Without ring	10	80	30	16	1.32	10	133
409-9745	TKJR-2	¥ 2,814	¥ 3,040	With ring	10	80	30	15	2.11	10	140


Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Ring Catch "Carabiner"



TKB-1 (without ring)



- Features**
- A spring hook.
  - The opening part returns with the force of the mechanical spring.
- Use**
- Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
- Materials**
- Stainless Steel (SUS304)
- Origin**
- China

**Warning**  
• It cannot be used as a safety belt.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	D (mm)	L (mm)	W (mm)	S (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
431-5898	TKB-1	¥ 3,703	¥ 4,000	Without ring	10	90	36	21	1.32	10	153
431-5901	TKB-2	¥ 4,351	¥ 4,700	With ring	10	90	36	19	2.11	10	164

Contact us: 0120-509-849 <http://www.orange-book.com/>

Hardware

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

Handles

Keys

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers