


TRUSCO

Stock
38,650
Items

Driving Rod U Type



TUU-Y820

- Features
- Since it is a U shape, secure it firmly.
- Use
- Optimum for pulling ropes and wires, etc. to the ground.
 - Various tents, tarp setting, gardening, compartment rope installation, and the like.
- Materials
- Steel
 - Surface Treatment: Unichrome
- Origin
- China

Example



Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Diameter (mm)	Length on a side (mm)	Width (mm)	SPQ (piece)	Weight (g)
275-3651	TUU-Y815	¥231	¥250	8	150	110	120	120
275-3669	TUU-Y820	¥278	¥300	8	200	120	75	150

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

Stock
38,650
Items

Rope Stopper U Type



TRU-S615

- Features
- It is made of stainless steel and resistant to rust.
- Use
- It is used for pulling and fixing ropes, etc. to the ground.
 - Various tents, tarp setting, gardening, compartment rope installation, and the like.
- Materials
- Stainless Steel (SUS304)
- Origin
- Japan

Example



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Diameter (mm)	Width (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
275-3839	TRU-S610	¥694	¥750	6	21	100	100	45
275-3847	TRU-S615	¥694	¥750	6	21	150	100	50
275-3855	TRU-S620	¥694	¥750	6	21	200	100	58

Contact us:0120-509-849 <http://www.orange-book.com/>

YUTAKA

Stock
1,604
Items

Hammering Stick U Type

- Features
- A bracket that is hammered when fixing a rope, a net, etc., to the ground, etc.
- Use
- Fixing a rope, a net, etc., to the ground.
- Materials
- Steel
 - Surface Treatment: Plated Finishing
- Origin
- Japan



KG-27

Order Unit: 1 Piece

YUTAKA MAKE Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Diameter (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
794-6091	KG-27	¥144	-	5	100	100	31
794-6104	KG-28	¥474	-	8	250	50	193

Contact us:072-441-2220 <http://www.yutakamake.co.jp/>


DAIDOHANT

Stock
357
Items

Heteromorphic J Type Rope Stopper

- Features
- The pull-out strength has been improved with a variant type (J type head).
- Use
- For fixing a rope, a wire, etc.
 - For installing an intrusion prevention rope.
- Materials
- Steel
 - Surface Treatment: Unichrome
- Origin
- China

Example



10168019

Order Unit: 1 Piece

DAIDOHANT Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Diameter (mm)	Fold back length (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
471-2609	10168019	¥140	-	6	40 to 50	150	10	40
471-2617	10168020	¥162	-	6	40 to 50	200	10	50
471-2625	10168021	¥173	-	6	40 to 50	240	10	60

Contact us:06-6821-3037 <http://www.daidohant.com/>