

# Suspension Brackets (screw fastened type)

Stock 223 Items

2-981

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items** **Plate Hook**


RoHS



- Features**
- Possible to install even on a narrow installation surface.
  - Since it is a no-counterbore type, please use screws such as a flat head screw, etc.
- Use**
- Set up on the wall, floor, pillar, etc., as a terminal metal fitting for the chain, wire, and rope.
- Materials** • **Stainless Steel (SUS304)** **Origin** • Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION



Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	A (mm)	B (mm)	P (mm)	H (mm)	d (mm)	Handling load (N/kgf)	SPQ (piece)	Weight (g)
380-3970	TPTF-4	¥ 861	¥ 930	4	34	10	24.0	26	4	98/10	20	10
380-3988	TPTF-5	¥ 954	¥ 1,030	5	40	12	28.5	32	5	147/15	20	18
380-3996	TPTF-6	¥ 1,130	¥ 1,220	6	44	14	32.0	37	5	196/20	20	28
380-4003	TPTF-8	¥ 1,361	¥ 1,470	8	50	16	36.0	49	6	294/30	10	54
380-3961	TPTF-10	¥ 1,685	¥ 1,820	10	58	18	40.0	58	8	490/50	10	91

Contact us: 0120-509-849 <http://www.orange-book.com/>

MIZUMOTO MACHINE **Stock 529 Items** **Plate Hook**


RoHS



- Features**
- Possible to install even on a narrow installation surface.
  - Since it is a no-counterbore type, please use screws such as a flat head screw, etc.
- Use**
- Set up on the wall, floor, pillar, etc., as a terminal metal fitting for the chain, wire, and rope.
- Materials** • **Stainless Steel (SUS304)** **Origin** • Taiwan

Order Unit: 1 Piece

MIZUMOTO MACHINE MFG.Co.Ltd



Order Code	Item No.	Price (per piece)	MSRP (per piece)	L (mm)	W1 (mm)	W2 (mm)	H (mm)	S1 (mm)	S2 (mm)	d (mm)	T (mm)	D (mm)	Handling load (N/kgf)	SPQ (piece)	Weight (g)
378-9373	B-2103	¥ 746	¥ 880	7.5	25.5	18	20	6.5	8.5	3	2	3	29.4/3	20	4

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>

MIZUMOTO MACHINE **Stock 529 Items** **Coat Hook (CHF)**


RoHS



- Features**
- It is made of stainless steel, rustless, and excellent in durability.
- Use**
- For a coat hook.
  - For hanging items.
- Materials** • **Stainless Steel (SUS304)**
- Accessories** • Countersunk wood screw x 2
- Origin** • China

Order Unit: 1 Piece

MIZUMOTO MACHINE MFG.Co.Ltd



Order Code	Item No.	Price (per piece)	MSRP (per piece)	L (mm)	W (mm)	B (mm)	H (mm)	t1 (mm)	t2 (mm)	D (mm)	Allowable Load (kN)	SPQ (piece)	Weight (g)
833-7821	B-2517	¥ 400	¥ 470	17	30	19	21	3.5	2.5	3.5	0.08	20	10.5
833-7822	B-2518	¥ 492	¥ 580	25	40	27	28	4.0	3.0	3.5	0.15	20	27.0

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>

SUGATSUNE **Stock 766 Items** **Hook**


RoHS



- Features**
- Since it is separated in 2 ways, it can hang 2 items with one hook.
- Use**
- Working facilities, production facilities, machinery equipment, in an office, hospitals, etc.
- Materials** • **Stainless steel (SCS13)**
- Accessories** • Cross Recess Round Countersunk Wood Screw (stainless steel)
- Origin** • Japan

Order Unit: 1 Piece

(Price revision date: May, 2015) SUGATSUNE KOGYO Co.Ltd.



Order Code	Item No.	Price (per piece)	MSRP (per piece)	A (mm)	C (mm)	D (mm)	E (mm)	H (mm)	H1 (mm)	P1 (mm)	d (mm)	Handling load (N/kgf)	SPQ (piece)	Weight (g)
440-3754	EW-65E	¥ 2,916	¥ 2,700	65	6.5	25	4	33	20	36	3.6	196/20	10	52
440-3762	EW-80E	¥ 3,348	¥ 3,100	80	8.0	32	5	42	25	44	4.2	196/20	10	93

Contact us: 03-3851-1122 <http://www.sugatsune.co.jp/>

SUGATSUNE **Stock 766 Items** **Hook**


RoHS



- Features**
- Since both the 2-separated tip part and the neck part can be used as a hook, it can hang 3 items with one hook.
- Use**
- Working facilities, production facilities, machinery equipment, in an office, hospitals, etc.
- Materials** • **Stainless steel (SCS14)**
- Accessories** • Cross Recess Round Countersunk Wood Screw (stainless steel)
- Origin** • Japan

Order Unit: 1 Piece

(Price revision date: May, 2015) SUGATSUNE KOGYO Co.Ltd.



Order Code	Item No.	Price (per piece)	MSRP (per piece)	D1 (mm)	P1 (mm)	P2 (mm)	d2 (mm)	W1 (mm)	W2 (mm)	d (mm)	Handling load (N/kgf)	SPQ (piece)	Weight (g)
440-3738	EU-50	¥ 2,948	¥ 2,730	38	7	20	7.4	22	38	4.0	196/20	20	42
440-3746	EU-72	¥ 4,903	¥ 4,540	52	10	34	8.6	32	56	4.6	294/30	10	118

Contact us: 03-3851-1122 <http://www.sugatsune.co.jp/>