

Valve Display Plates

The number next to the logo mark indicates items in stock for each brand.

Valves

Screwed Type Pipe Fittings

High Pressure Joints

Welding Fittings

Flanges

Flexible Metal Hoses

Piping Joints for Minor Diameters

Sanitary Pipe Couplings

PVC Pipes

PVC Pipe Joints

PVC Valves

Joints for Water Piping

Protect Accessories for Plumbing

Support Accessories for Plumbing

Maintenance Accessories for Plumbing

Air Conditioning Materials

Valve Pipe Identifying Goods

Spray Nozzles

TRUSCO Stock 38,650 Items

Valve Opening-and-closing Display Board



Features •Used raw materials resistant to shock which are excellent in water resistance and durability.
Specs •Top Hole (4mm) x 1 Location
Origin •Japan

Warning
 •Mounting fixtures are sold separately.

Aluminum Specs •Duplex Printing Materials •Aluminum

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Color	L x W (mm)	Thickness (mm)	Q'ty Per Set (sheet)	SPQ (set)	Weight (g/set)
489-5312	T857-01	¥1,111	¥1,200	Blue	50 x 50	1.5	5	1	55
489-5321	T857-02	¥1,111	¥1,200	Red	50 x 50	1.5	5	1	55
489-5339	T857-03	¥1,111	¥1,200	Blue	50 x 50	1.5	5	1	55
489-5347	T857-04	¥1,111	¥1,200	Red	50 x 50	1.5	5	1	55




Recycled polypropylene Materials •Recycled polypropylene (recycled material 50%)

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Color	L x W (mm)	Thickness (mm)	Q'ty Per Set (sheet)	SPQ (set)	Weight (g/set)
415-5696	T854-01	¥741	¥800	Blue	50 x 50	2	5	20	24
415-5700	T854-02	¥741	¥800	Red	50 x 50	2	5	20	24
415-5718	T854-03	¥741	¥800	Green	50 x 50	2	5	20	24
415-5726	T854-04	¥741	¥800	Blue	50 x 50	2	5	20	24
415-5734	T854-05	¥741	¥800	Red	50 x 50	2	5	20	24
415-5742	T854-06	¥741	¥800	Green	50 x 50	2	5	20	24
415-5424	T854-60	¥741	¥800	Blue	50 x 50	2	5	50	19
415-5394	T854-61	¥741	¥800	Red	50 x 50	2	5	50	19
415-5432	T854-62	¥741	¥800	Green	50 x 50	2	5	20	19
415-5441	T854-63	¥741	¥800	Blue	50 x 50	2	5	20	19
415-5408	T854-64	¥741	¥800	Red	50 x 50	2	5	50	19
415-5416	T854-65	¥741	¥800	Green	50 x 50	2	5	50	19
415-5921	T886-34	¥833	¥900	White	40 x 80	2	10	50	60
415-5904	T886-40	¥926	¥1,000	White	50 x 50	2	10	50	24
415-5891	T886-42	¥833	¥900	White	80 x 40	2	10	50	60
415-5912	T886-54	¥741	¥800	White	50 x 25	2	10	50	10
489-5207	T459-15	¥417	¥450	White	60 x 38	2	5	50	23
489-5444	T886-43	¥389	¥420	White	60 x 40	2	5	50	23
489-5452	T886-49	¥324	¥350	White	45 x 30	2	5	50	15

[White Plain Board]



Acrylic Materials •Acrylic

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Color	L x W (mm)	Thickness (mm)	Q'ty Per Set (sheet)	SPQ (set)	Weight (g/set)
489-5215	T459-26	¥370	¥400	White	70 x 47	2.5	5	50	44
489-5223	T459-30	¥370	¥400	White	65 x 45	2.5	5	50	46


Contact us:0120-509-849 <http://www.orange-book.com/>

GREEN CROSS Stock 1,404 Items

Valve Open/Close Tag (with ring)



Features •It is lightweight and has excellent durability. It adopts aluminium material that can be used in high temperatures.
Specs •With stainless steel ring 15mmφ x 2
 •Duplex Printing
Materials •Aluminum
Origin •Japan



JAPAN GREEN CROSS,INC.

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Color (open)	Color (close)	L x W (mm)	Thickness (mm)	SPQ (set)	Weight (g/set)
382-0459	162011	¥1,080	¥1,000	Blue	Red	65 x 65	0.8	1	21
382-0467	162012	¥1,080	¥1,000	Red	Green	65 x 65	0.8	1	21
382-0475	162013	¥1,080	¥1,000	Red	Blue	65 x 65	0.8	1	21
382-0483	162014	¥1,080	¥1,000	Green	Red	65 x 65	0.8	1	21

Contact us:0120-66-7971 <http://www.jgc-inc.co.jp/>