

L Type Clamps (for woodworking)


Stock 412 Items

4-1791

Prices displayed include 8% tax.

TRUSCO
 Stock 38,650 Items

Clamp for Woodworking



- Features**
- The tightening part is covered with plastic to prevent damages.
 - It is made so that it becomes always parallel to the clamp surface.
 - When the handle is inclined to the outside, the mouth opens and when inclined to the inside, the mouth closes.
- Materials**
- Cold rolled steel material
 - Resin
- Origin**
- Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	Throat (mm)	Frame Dimension (mm)		SPQ (piece)	Weight (kg)
							A	B		
490-0936	PJH-30	¥ 5,804	¥ 6,270	460	300	95	29	9	6	2.03
490-0944	PJH-60	¥ 6,879	¥ 7,430	760	600	95	29	9	6	2.57
490-0952	PJH-100	¥ 8,563	¥ 9,250	1160	1000	95	29	9	6	3.28
490-0961	PJH-125	¥ 9,257	¥ 10,000	1410	1250	95	29	9	6	3.37
490-0979	PJH-150	¥ 10,266	¥ 11,090	1660	1500	95	29	9	4	4.18
490-0987	PJH-200	¥ 12,377	¥ 13,370	2160	2000	95	29	9	2	5.07
490-0995	PJH-250	¥ 15,043	¥ 16,250	2660	2500	95	29	9	2	5.96

Stopper

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Model	SPQ (piece)	Weight (g)
490-1002	PJHSP	¥ 278	¥ 300	PJH-30-60-100-125-150-200-250	10	20

Platform

Order Unit: 1 Piece


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Model	SPQ (piece)	Weight (g)
490-1011	PJHPF	¥ 278	¥ 300	PJH-30-60-100-125-150-200-250	10	20

Contact us: 0120-509-849 <http://www.orange-book.com/>



KAKURI
 Stock 115 Items

Plating Bar Clamp



- Features**
- Optimum for stopper clamping when stack-cutting of plates or when joining plates.
 - Because the surface is treated with nickel chrome plating, it is difficult to rust.
- Materials**
- Iron (nickel chrome plate treatment)
- Origin**
- Japan



Order Unit: 1 Piece


KAKURI Corporation

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	Throat (mm)	Frame Dimension (mm)		SPQ (piece)	Weight (g)
							A	B		
784-8111	13643	¥ 1,589	-	380	300	25	7	7	10	265
784-8129	13644	¥ 1,675	-	440	360	25	7	7	10	290
784-8137	13645	¥ 2,347	-	530	450	30	8	8	10	420
784-8145	13647	¥ 2,777	-	700	600	33	16	6	10	740
784-8153	13648	¥ 3,153	-	850	750	33	16	6	10	850
784-8161	13649	¥ 3,636	-	1000	900	33	16	6	10	960

Contact us: 0256-34-6113 <http://www.kakuri.co.jp/>

KAKURI
 Stock 115 Items

"Brass Gad"



- Features**
- Optimum for stopper clamping when stack-cutting of plates or when joining plates.
- Materials**
- Brass
- Origin**
- Japan



Order Unit: 1 Piece

KAKURI Corporation

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	Throat (mm)	Frame Dimension (mm)		SPQ (piece)	Weight (g)
							A	B		
784-8170	13709	¥ 818	-	185	127	13	4	4	10	50
784-8188	13710	¥ 993	-	250	215	13	5	5	10	90
784-8196	13711	¥ 1,014	-	310	275	13	5	5	10	100

Contact us: 0256-34-6113 <http://www.kakuri.co.jp/>