

Prices displayed include 8% tax.

For Tap Holder, see p. 1-392 to 395

TRUSCO Stock 38,650 Items


Bending Tap Removal Tool (three claws)



- Features**
- A tool that easily removes the bent tap without damaging the ridge when the middle of the tap bend.
 - Since the claw uses a special steel wire, it has a high twisting strength and does not easily break, so you can easily remove the bent tap that is firmly lodged in.
 - In the unlikely event that the claw is damaged, it can still be used many times until it becomes short. Moreover, since it can be easily exchanged with the replacement claw, it is very economical.
 - Exclusive for hand tap.
- Use**
- To extract the broken hand tap.
- Materials**
- Medium Carbon Steel (S45C)
- Origin**
- Japan



PT3-3



Warning

- Cannot be used for spiral pointed-tap, jet tap, pointed-tap.

Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Used Tap Handle	Applicable Tap Dimension	SPQ (piece)	Weight (g)
231-8989	PT3-3	¥2,694	¥2,910	45	TH-6	3mm (1/8)	10	5
231-9004	PT3-4	¥2,694	¥2,910	53	TH-6	4mm (5/32)	10	5
231-9021	PT3-5	¥2,694	¥2,910	55	TH-6	5mm (3/16)	10	5
231-9047	PT3-6	¥2,694	¥2,910	55	TH-6	6mm (1/4)	10	14
231-9063	PT3-8	¥2,870	¥3,100	80	TH-10	8mm (5/16)	10	33
231-9080	PT3-10	¥3,370	¥3,640	85	TH-10	10mm (7/16)	10	47
231-9101	PT3-12	¥3,777	¥4,080	98	TH-13	12mm (1/2)	1	100

Bent Tap Removal Tool with Three Claws (for three grooves) Replacement Claw

Order Unit: 1 Set (Price revision date: Jan, 2016)

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible Body	Q'ty Per Set (piece)	SPQ (set)	Weight (g/set)
231-8997	PT3-3K	¥1,472	¥1,590	PT3-3	3	10	2
231-9012	PT3-4K	¥1,472	¥1,590	PT3-4	3	10	2
231-9039	PT3-5K	¥1,472	¥1,590	PT3-5	3	10	2
231-9055	PT3-6K	¥1,472	¥1,590	PT3-6	3	10	2
231-9071	PT3-8K	¥1,472	¥1,590	PT3-8	3	10	2
231-9098	PT3-10K	¥1,934	¥2,090	PT3-10	3	10	4
231-9110	PT3-12K	¥1,926	¥2,080	PT3-12	3	10	6

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items


Removing Tools for Folded Tap (4 piece claw)



- Features**
- A tool that easily removes the bent tap without damaging the ridge when the middle of the tap bend.
 - Since the claw uses a special steel wire, it has a high twisting strength and does not easily break, so you can easily remove the bent tap that is firmly lodged in.
 - In the unlikely event that the claw is damaged, it can still be used many times until it becomes short. Moreover, since it can be easily exchanged with the replacement claw, it is very economical.
 - Exclusive for hand tap.
- Use**
- To extract the broken hand tap.
- Materials**
- Medium Carbon Steel (S45C)
- Origin**
- Japan



PT4-8



Warning

- Cannot be used for spiral pointed-tap, jet tap, pointed-tap.

Order Unit: 1 Piece (Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Used Tap Handle	Applicable Tap Dimension	SPQ (piece)	Weight (g)
231-9128	PT4-6	¥2,694	¥2,910	55	TH-6	6mm (1/4)	10	15
231-9144	PT4-8	¥2,870	¥3,100	76	TH-10	8mm (5/16)	10	30
231-9161	PT4-10	¥3,370	¥3,640	85	TH-10	10mm (3/8)	10	48
231-9187	PT4-12	¥3,777	¥4,080	100	TH-13	12mm (1/2)	1	100
231-9209	PT4-14	¥4,629	¥5,000	106	TH-19	14mm (9/16)	1	140
231-9225	PT4-16	¥5,045	¥5,450	110	TH-19	16mm (5/8)	1	160
231-9241	PT4-18	¥6,526	¥7,050	125	TH-19	18mm (3/4)	1	220
231-9268	PT4-20	¥7,146	¥7,720	130	TH-19	20mm (13/16)	1	250

Fold tap removal tool Four claws (for four grooves) Replacement claw

Order Unit: 1 Set (Price revision date: Jan, 2016)

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible Body	Q'ty Per Set (piece)	SPQ (set)	Weight (g/set)
231-9136	PT4-6K	¥1,657	¥1,790	PT4-6	4	10	5
231-9152	PT4-8K	¥1,657	¥1,790	PT4-8	4	10	11
231-9179	PT4-10K	¥2,203	¥2,380	PT4-10	4	10	11
231-9195	PT4-12K	¥2,203	¥2,380	PT4-12	4	10	21
231-9217	PT4-14K	¥2,898	¥3,130	PT4-14	4	10	21
231-9233	PT4-16K	¥2,898	¥3,130	PT4-16	4	10	26
231-9250	PT4-18K	¥3,675	¥3,970	PT4-18	4	10	51
231-9276	PT4-20K	¥3,675	¥3,970	PT4-20	4	10	51

Contact us: 0120-509-849 <http://www.orange-book.com/>



PT4-6K

(replacement claws, included 4 pieces)