


The number next to the logo mark indicates items in stock for each brand.



Stock  
38,650  
Items

## EPDM Sponge Roll



TER-3510

**Features** •Excellent in water repency, weather resistance and sound proof. •Surface coating type non-migratory EPDM sponge.  
**Use** •Cushioning material, protection materials.  
**Specs** •Working Temperature Range: -20 to 80° C •Color: Black  
**Materials** •Ethylene Propylene Rubber (EPDM)  
**Origin** •Japan

### Warning

•Has some errors from the display size on the characteristics of the commodity.

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION


Order Code	Item No.	Price (per roll)	MSRP (per roll)	Thickness (mm)	Width (mm)	Length (m)	SPQ (roll)	Weight (kg)
754-2640	TER-3510	¥16,941	¥18,300	3	500	10	1	2.53
754-2682	TER-31010	¥29,067	¥31,400	3	1000	10	1	5.06
754-2658	TER-5510	¥22,125	¥23,900	5	500	10	1	3.18
754-2691	TER-51010	¥39,528	¥42,700	5	1000	10	1	6.36
754-2666	TER-1055	¥16,663	¥18,000	10	500	5	1	2.73
754-2674	TER-10105	¥28,512	¥30,800	10	1000	5	1	5.46

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock  
1,144  
Items

## EPDM Sponge



KSEP-3021

**Features** •Excellent in weather resistance/heat resistance/chemical resistance.  
**Use** •Cushioning material, protection material.  
**Specs** •Working Temperature Range: -20 to 60° C •Color: Black  
**Materials** •Ethylene Propylene Rubber (EPDM) •Origin •China

Order Unit: 1 Sheet

HIKARI Co.Ltd.

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Thickness (mm)	Width (mm)	Length (mm)	SPQ (sheet)	Weight (g)
473-9451	KSEP-1016	¥100	-	5	100	100	5	5
473-9507	KSEP-2016	¥321	-	5	200	200	5	22
473-9540	KSEP-3016	¥501	-	5	300	300	5	47
473-9442	KSEP-1011	¥151	-	10	100	100	5	10
473-9493	KSEP-2011	¥633	-	10	200	200	5	38
473-9531	KSEP-3011	¥954	-	10	300	300	5	87
473-9485	KSEP-12011	¥21,662	-	10	1000	2000	5	2001
473-9469	KSEP-1021	¥281	-	20	100	100	5	20
473-9515	KSEP-2021	¥1,184	-	20	200	200	5	82
473-9558	KSEP-3021	¥1,415	-	20	300	300	5	180
473-9477	KSEP-1031	¥442	-	30	100	100	5	28
473-9523	KSEP-2031	¥1,705	-	30	200	200	5	112
473-9566	KSEP-3031	¥2,096	-	30	300	300	5	264

Contact us:06-6764-1531 <http://www.osaka-hikari.co.jp/>



Stock  
274  
Items

## EPDM Sponge



Stock  
193  
Items

## Sealing Material



EPN-01

**Features** •Excellent in weather resistance, heat resistance, and chemical resistance.  
**Use** •Cushioning material and protection material.  
**Specs** •With adhesive tape •Working Temperature Range: -20 to 80° C •Color: Black  
**Materials** •Ethylene Propylene Rubber (EPDM)  
**Origin** •Japan



E-7003

**Features** •Prevents sound from leaking by sealing the gap between metal sheet, resin sheet, and plaster board.  
**Use** •Sound leaking prevention.  
**Specs** •With adhesive tape •Working Temperature Range: -40 to 110° C •Color: Black  
**Materials** •Foam Rubber (EPDM series)  
**Origin** •Japan

Order Unit: 1 Sheet

Wakisangyo Co., Ltd.

Order Unit: 1 Roll

INOAC CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Thickness (mm)	Width (mm)	Length (mm)	SPQ (sheet)	Weight (g)
836-3019	EPN-01	¥226	-	5	30	300	50	35
836-3020	EPN-02	¥352	-	10	30	300	50	65

Order Code	Item No.	Price (per roll)	MSRP (per roll)	Thickness (mm)	Width (mm)	Length (mm)	SPQ (roll)	Weight (g)
417-2434	E-7003	¥447	-	10	20	2000	125	42

Contact us:06-6723-9879 <http://www.waki-diy.co.jp/>


Contact us:03-3492-9171 <http://www.inoac.co.jp/>

## Made to order For inquiries regarding special shape processing of rubber material

Akitsu Industry Co.Ltd.

To suit customer need, we will perform special shape processing of various type of rubber such as natural rubber, CR rubber, NBR rubber, EPDM rubber, silicon rubber, fluorine rubber, and urethane rubber.

Ring-shaped Processed Item    Frame-shaped Processed Item    Various Three-dimensional Processed Item



Akitsu Industry Co.Ltd.

TEL :06-4309-2212  
FAX :06-4309-2218