

Welded Rings

The number next to the logo mark indicates items in stock for each brand.

Hardware

TRUSCO



Stock 38,650 Items


Round Link



Features • Since the connection part is welded, it is strong.
 Use • As a tip metal fitting for rope and the like.
 Materials • **Stainless Steel (SUS304)**
 Origin • Japan



TMR-6-40



Order Unit: 1 Bag

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	L (mm)	Working Load (kN)	Qty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
274-9947	TMR-2-20	¥ 269	¥ 290	2.0	20	0.02	2	20	3
274-9955	TMR-2.5-20	¥ 287	¥ 310	2.5	20	0.05	2	20	5
274-9963	TMR-3-25	¥ 334	¥ 360	3.0	25	0.20	2	20	10
274-9971	TMR-4-30	¥ 342	¥ 370	4.0	30	0.39	2	20	20
274-9980	TMR-5-35	¥ 259	¥ 280	5.0	35	0.59	1	20	19
274-9998	TMR-6-40	¥ 287	¥ 310	6.0	40	0.78	1	20	31
275-0007	TMR-7-45	¥ 352	¥ 380	7.0	45	0.98	1	20	51
275-0015	TMR-8-45	¥ 444	¥ 480	8.0	45	1.18	1	20	66
275-0023	TMR-9-50	¥ 620	¥ 670	9.0	50	1.76	1	10	92
275-0031	TMR-10-50	¥ 814	¥ 880	10.0	50	1.96	1	10	117
275-0040	TMR-11-60	¥ 889	¥ 960	11.0	60	2.45	1	10	170
275-0058	TMR-12-60	¥ 1,481	¥ 1,600	12.0	60	2.94	1	10	205
275-0066	TMR-13-60	¥ 1,666	¥ 1,800	13.0	60	4.90	1	10	248

Contact us: 0120-509-849 <http://www.orange-book.com/>

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

MIZUMOTO MACHINE



Stock 529 Items

Round Link




Features • Since the connection part is welded, it is strong.
 Use • As a tip metal fitting for rope and the like.

Materials • **Stainless Steel (SUS304)**
 Origin • Japan



B-1964



Order Unit: 1 Bag

(Price revision date: Jan, 2016) MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	L (mm)	Working Load (kN)	Qty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
378-9217	B-1964	¥ 336	¥ 395	2.0	40	0.010	3	20	9.6
378-9225	B-1967	¥ 361	¥ 425	2.5	30	0.040	3	20	12.0
378-9039	B-1908	¥ 174	¥ 205	3.0	20	0.250	1	20	4.0
378-8300	B-1313	¥ 213	¥ 250	3.0	40	0.100	1	20	8.0
378-9896	B-2332	¥ 247	¥ 290	3.0	50	0.080	1	20	9.0
378-8415	B-1414	¥ 208	¥ 245	4.0	20	0.690	1	20	8.0
378-9047	B-1910	¥ 217	¥ 255	4.0	25	0.490	1	20	9.0
378-8865	B-1701	¥ 238	¥ 280	4.0	35	0.250	1	20	12.0
378-9284	B-1998	¥ 339	¥ 400	4.0	60	0.120	1	20	20.0
378-8873	B-1702	¥ 271	¥ 320	5.0	20	1.960	1	20	13.0
378-9641	B-2213	¥ 285	¥ 335	5.0	25	0.980	1	20	15.0
378-9675	B-2220	¥ 293	¥ 345	5.0	30	0.780	1	20	17.0
378-9021	B-1899	¥ 332	¥ 390	5.0	40	0.490	1	20	22.0
378-9659	B-2214	¥ 349	¥ 410	5.0	45	0.290	1	20	24.0
378-8318	B-1316	¥ 378	¥ 445	5.0	50	0.250	1	20	26.0
378-8326	B-1317	¥ 438	¥ 515	5.0	60	0.150	1	20	31.0
378-8881	B-1703	¥ 332	¥ 390	6.0	30	1.370	1	20	25.0
378-8334	B-1318	¥ 417	¥ 490	6.0	50	0.490	1	20	41.0
378-8342	B-1319	¥ 458	¥ 540	6.0	60	0.340	1	20	45.0
378-8890	B-1704	¥ 561	¥ 660	8.0	40	1.960	1	20	61.0
378-9667	B-2219	¥ 1,095	¥ 1,290	10.0	60	1.520	1	10	138.0

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>

Handles

Keys

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

TRUSCO



Stock 38,650 Items

Oval Link




Features • Compared with a round ring with the same wire diameter, working load increases by approx. 2-fold.
 • Since it is welded at the connection part, it is strong.
 Use • For a connecting/hanging brackets for chains, ropes, etc.
 Materials • **Stainless Steel (SUS304)**
 Origin • China



TOL-3

Example



Order Unit: 1 Bag

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	P (mm)	W (mm)	Working Load (kN)	Qty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
300-9297	TOL-3	¥ 334	¥ 360	3	19	6	0.69	2	20	6
300-9301	TOL-4	¥ 361	¥ 390	4	26	12	0.88	2	20	16
300-9319	TOL-5	¥ 509	¥ 550	5	28	16	1.47	2	20	28
300-9327	TOL-6	¥ 361	¥ 390	6	31	18	2.45	1	20	23
300-9335	TOL-8	¥ 509	¥ 550	8	50	30	3.43	1	20	62
300-9343	TOL-9	¥ 741	¥ 800	9	50	32	4.90	1	10	81
300-9351	TOL-10	¥ 907	¥ 980	10	60	40	5.88	1	10	122
300-9360	TOL-11	¥ 1,213	¥ 1,310	11	70	45	6.37	1	10	167
300-9378	TOL-12	¥ 1,750	¥ 1,890	12	80	50	7.35	1	10	223

Contact us: 0120-509-849 <http://www.orange-book.com/>

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers