

The number next to the logo mark indicates items in stock for each brand.

TRUSCO




Stock 38,650 Items

Eye Snap



TAS-2



- Features**
- Since the eye part rotates, it is used for untwisting a chain, etc.
 - With the spring hook, it can easily open/close.
- Use**
- Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
- Materials**
- **Stainless Steel (SUS304)**
- Origin**
- China



Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W (mm)	S (mm)	H (mm)	d (mm)	t (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
328-6169	TAS-0	¥ 907	¥ 980	3	57	18	5	10	11	3	0.20	20	17
328-6177	TAS-1	¥ 954	¥ 1,030	4	71	23	6	12	14	4	0.29	20	30
328-6185	TAS-1.5	¥ 1,009	¥ 1,090	4	87	28	9	14	16	4	0.29	20	46
328-6193	TAS-2	¥ 1,047	¥ 1,130	5	90	28	9	17	18	4	0.39	20	49

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO




Stock 38,650 Items

Swivel Snap



TSS-1



- Features**
- Since the eye portion rotates with a swivel, chains do not come through.
- Use**
- Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
- Materials**
- **Stainless Steel (SUS304)**
- Origin**
- Taiwan



Order Unit: 1 Bag

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	L (mm)	W (mm)	S (mm)	H (mm)	d (mm)	Working Load (kN)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
275-0635	TSS-0	¥ 2,490	¥ 2,690	4	66	22	5	12	13.0	0.20	2	20	68
275-0643	TSS-1	¥ 2,926	¥ 3,160	5	85	28	9	19	19.0	0.29	2	20	116
275-0651	TSS-2	¥ 1,999	¥ 2,160	5	98	38	12	20	21.5	0.39	1	20	91
275-0660	TSS-3	¥ 2,499	¥ 2,700	7	118	46	14	23	23.0	0.49	1	10	151

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO




Stock 38,650 Items

Swivel Snap



TBRF-1



- Features**
- Since the eye part rotates, it is used for untwisting a chain, etc.
 - With the spring hook, it can easily open/close.
- Use**
- Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
- Materials**
- **Brass**
- Origin**
- China



Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W (mm)	S (mm)	R (mm)	H (mm)	d (mm)	t (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
409-9648	TBRF-1	¥ 463	¥ 500	3.5	60	22	7	3.0	12.5	10	4.5	0.15	20	21
409-9656	TBRF-2	¥ 573	¥ 620	4.0	70	26	7	2.5	14.0	12	5.5	0.20	20	34

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO




Stock 38,650 Items

Swivel



TRMS-6



- Features**
- Remove the twist as it rotates.
- Use**
- The center part rotates and you may use it as setting back lay.
- Materials**
- **Stainless Steel (SUS304)**
- Origin**
- Taiwan

Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L1 (mm)	W1 (mm)	L2 (mm)	W2 (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
409-9788	TRMS-3	¥ 500	¥ 540	3	27.5	14	5.5	8	0.29	20	5
409-9796	TRMS-4	¥ 723	¥ 780	4	50.0	19	12.0	11	0.78	20	17
409-9800	TRMS-5	¥ 796	¥ 860	5	59.0	23	14.0	13	1.18	20	35
409-9818	TRMS-6	¥ 935	¥ 1,010	6	66.0	27	15.0	15	1.76	20	54
409-9826	TRMS-8	¥ 1,213	¥ 1,310	8	90.0	35	21.0	20	2.45	20	124
409-9834	TRMS-9	¥ 1,602	¥ 1,730	9	104.0	40	23.0	22	2.94	10	195
409-9753	TRMS-10	¥ 2,138	¥ 2,310	10	115.0	44	27.0	24	3.92	10	252
409-9761	TRMS-12	¥ 3,138	¥ 3,390	12	129.0	49	28.0	25	6.86	10	372
409-9770	TRMS-13	¥ 3,518	¥ 3,800	13	150.0	58	33.0	33	8.82	10	546

Contact us:0120-509-849 <http://www.orange-book.com/>