

Replacement Blade for Handsaws

For Saw Main Bodies, see p. 4-1146 to 1148

The number next to the logo mark indicates items in stock for each brand.

Cutting Supplies

Cutting Wheels

Tip Saws

Diamond Cutters

Metal Saws

Band Saws

Machine Saws

Hand Hacksaws

Saw Blades

Air Saw Blades

Jig Saw Blades



Please wear protective equipment to use safely.



Stock 2,057 Items

Replacement Blade for Handsaws



3905-250-24-100P

Estimated Unit Price per Sheet
¥262

- Features**
- Low price common use 100% high speed steel handsaw.
 - More resilient than traditional high-speed steel saw blades, making it hard to break.
- Use**
- For iron working, pipes such as stainless pipes/for cutting electrical pipe work.
- Specs**
- Compatible Model: 250mm wide Hacksaw
- Materials**
- Blade Edge/Saw Body: All High Speed Steel HSS
- Origin**
- China

Order Unit: 1 Box

Snap-On Tools JAPAN K.K.


Order Code	Item No.	Price (per box)	MSRP (per box)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Q'ty Per Box (sheet)	Weight (kg/box)
354-1282	3905-250-24-100P	¥26,198	¥30,000	24	250	263	100	1.5

Contact us: 03-5534-1301 <http://www.snapon.co.jp/>



Stock 38,650 Items

Replacement Blade for Handsaws



NS3906-250-32-5P (including 5 sheets)

Estimated Unit Price per Sheet
¥366



NS3906-250-32-100P (including 100 sheets)

Estimated Unit Price per Sheet
¥284

Estimated Unit Price per Sheet
¥392

- Features**
- By attaching a rake angle of 6 degrees, the bites are sharp and can cut smoothly.
 - Long lasting by using high-grade high-speed steel containing cobalt which is excellent in durability.
- Use**
- For cutting stainless steel, alloy steel and so on.
- Materials**
- Blade Edge: Bimetal with Cobalt
 - Saw Blade: Spring Steel
- Origin**
- Sweden

250mm width including 5 sheets Specs • Compatible Model: 250mm wide Hacksaw

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Bag (sheet)	Weight (kg/bag)
232-0266	NS3906-250-18-5P	¥1,831	¥2,260	18	250	263	0.65	5	80
232-0274	NS3906-250-24-5P	¥1,831	¥2,260	24	250	263	0.65	5	80
232-0282	NS3906-250-32-5P	¥1,831	¥2,260	32	250	263	0.65	5	80

250mm width including 100 sheets Specs • Compatible Model: 250mm wide Hacksaw

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Box (sheet)	Weight (kg/box)
232-0193	NS3906-250-18-100P	¥28,350	¥35,000	18	250	263	0.65	100	1.7
232-0207	NS3906-250-24-100P	¥28,350	¥35,000	24	250	263	0.65	100	1.7
232-0215	NS3906-250-32-100P	¥28,350	¥35,000	32	250	263	0.65	100	1.7

300mm width including 5 sheets Specs • Compatible Model: 300mm wide Hacksaw

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Bag (sheet)	Weight (kg/bag)
440-9825	NS3906-300-18-5P	¥1,960	¥2,420	18	300	313	0.65	5	104
440-9833	NS3906-300-24-5P	¥1,960	¥2,420	24	300	313	0.65	5	104
440-9841	NS3906-300-32-5P	¥1,960	¥2,420	32	300	313	0.65	5	104

300mm width including 100 sheets Specs • Compatible Model: 300mm wide Hacksaw

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Box (sheet)	Weight (kg/box)
232-0223	NS3906-300-18-100P	¥30,375	¥37,500	18	300	313	0.65	100	1.9
232-0231	NS3906-300-24-100P	¥30,375	¥37,500	24	300	313	0.65	100	1.9
232-0240	NS3906-300-32-100P	¥30,375	¥37,500	32	300	313	0.65	100	1.9

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 2,057 Items

Replacement Blade for Handsaws



3906-250-24-100 (250mm width)

Estimated Unit Price per Sheet
¥329



3906-300-24-100 (300mm width)

Estimated Unit Price per Sheet
¥349

- Features**
- By attaching a rake angle of 6 degrees, the bites are sharp and can cut smoothly.
 - Long lasting by using high-grade high-speed steel containing cobalt which is excellent in durability.
- Use**
- For iron working, pipes such as stainless steel pipes/for cutting electrical pipe construction.
- Materials**
- Blade Edge: Bimetal with Cobalt
 - Saw Blade: Spring Steel
- Origin**
- Sweden

250mm width Specs • Compatible Model: 250mm wide Hacksaw

Order Unit: 1 Box

Snap-On Tools JAPAN K.K.

Order Code	Item No.	Price (per box)	MSRP (per box)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Q'ty Per Box (sheet)	Weight (kg/box)
351-9660	3906-250-18-100	¥32,986	¥38,000	18	250	263	100	1.5
351-9678	3906-250-24-100	¥32,986	¥38,000	24	250	263	100	1.5
351-9686	3906-250-32-100	¥32,986	¥38,000	32	250	263	100	1.5

300mm width Specs • Compatible Model: 300mm wide Hacksaw

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Q'ty Per Box (sheet)	Weight (kg/box)
351-9694	3906-300-18-100	¥34,915	¥40,000	18	300	313	100	1.7
351-9708	3906-300-24-100	¥34,915	¥40,000	24	300	313	100	1.7
351-9716	3906-300-32-100	¥34,915	¥40,000	32	300	313	100	1.7

Contact us: 03-5534-1301 <http://www.snapon.co.jp/>