

Prices displayed include 8% tax.

For Oil Polishing Agents, see p. 5-1023 to 1025

TRUSCO Stock 38,650 Items

"Emery Buff" (for polishing metal and burring)



Com.eco Chemical Content Inspection .Com Drawing SDS

- Features**
- It is a cotton cloth buff that allows you to finish polishing of general metals with Tripoli or Emery (abrasive grains).
- Use**
- Iron base polishing, plating base, burring.
 - Working Tool: Straight-type grinder, double ended grinder, buff grinder.
- Origin**
- Japan



Warning

- Depending on the material fabric, colors may change but this does not affect quality.



TEB-100-4

Estimated Unit Price per Sheet
¥278 to ¥1,185

Order Unit: 1 Box (Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
261-6327	TEB-50-2	¥1,389	¥1,500	50 x 8 x 6.00	16000	5	20	50
261-6335	TEB-75-3	¥2,055	¥2,220	75 x 8 x 9.53	11000	5	20	100
261-6343	TEB-100-4	¥2,527	¥2,730	100 x 8 x 12.70	8000	5	20	275
261-6351	TEB-125-4	¥3,406	¥3,680	125 x 8 x 12.70	6500	5	20	340
261-6360	TEB-150-4	¥3,916	¥4,230	150 x 8 x 12.70	5500	5	20	520
289-9817	TEB-200-5	¥ 852	¥ 920	200 x 8 x 15.88	4000	1	20	210
289-9825	TEB-250-6	¥1,055	¥1,140	250 x 8 x 19.05	3200	1	20	336
289-9833	TEB-300-8	¥1,185	¥1,280	300 x 8 x 25.40	2700	1	20	384

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

"Brown Cotton Finishing Buff" (for metal finishing and glossy polishing)



Com.eco Chemical Content Inspection .Com Drawing SDS

- Features**
- A cotton cloth buff which can finish polish standard metals by applying a blue bar. It can be used for polishing of resin with tripoli for resin.
- Use**
- Mirror finishing of metal. Removal of processing scratches, etc. from resin.
 - Working Tool: Straight-type grinder, double ended grinder, buff grinder.
- Origin**
- Japan



Warning

- Depending on the material fabric, colors may change but this does not affect quality.



TTB-100-4

Estimated Unit Price per Sheet
¥239 to ¥1,092

Order Unit: 1 Box (Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
261-6378	TTB-50-2	¥1,194	¥1,290	50 x 7 x 6.00	16000	5	20	30
261-6386	TTB-75-3	¥1,426	¥1,540	75 x 7 x 9.53	11000	5	20	80
261-6394	TTB-100-4	¥2,138	¥2,310	100 x 7 x 12.70	8000	5	20	150
261-6408	TTB-125-4	¥2,841	¥3,070	125 x 7 x 12.70	6500	5	20	250
261-6416	TTB-150-4	¥3,277	¥3,540	150 x 7 x 12.70	5500	5	20	330
289-9931	TTB-200-5	¥ 870	¥ 940	200 x 7 x 15.88	4000	1	20	115
289-9949	TTB-250-6	¥ 990	¥1,070	250 x 7 x 19.05	3200	1	20	186
289-9957	TTB-300-8	¥1,092	¥1,180	300 x 7 x 25.40	2700	1	20	262

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items

"Calico Finishing Buff" (for non-ferrous metal finishing)



Com.eco Chemical Content Inspection .Com Drawing SDS

- Features**
- A cotton fabric calico finishing buff capable of mirror surface glossy finishing by applying a polishing agent for non-ferrous metals.
- Use**
- Mirror surface finishing of aluminum, brass, and zinc.
 - Working Tool: Straight-type grinder, double ended grinder, buff grinder.
- Origin**
- Japan



TKB-100-4

Estimated Unit Price per Sheet
¥122 to ¥703

Order Unit: 1 Box (Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter x Thickness x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
261-6424	TKB-50-2	¥ 611	¥ 660	50 x 2.5 x 6.00	16000	5	20	10
261-6432	TKB-75-3	¥ 703	¥ 760	75 x 2.5 x 9.53	11000	5	20	38
261-6441	TKB-100-4	¥1,037	¥1,120	100 x 2.5 x 12.70	8000	5	20	50
261-6459	TKB-125-4	¥1,213	¥1,310	125 x 2.5 x 12.70	6500	5	20	90
261-6467	TKB-150-4	¥1,462	¥1,580	150 x 2.5 x 12.70	5500	5	20	125
289-9841	TKB-200-5	¥ 435	¥ 470	200 x 2.5 x 15.88	4000	1	20	42
289-9850	TKB-250-6	¥ 648	¥ 700	250 x 2.5 x 19.05	3200	1	20	70
289-9868	TKB-300-8	¥ 703	¥ 760	300 x 2.5 x 25.40	2700	1	20	95

Contact us:0120-509-849 <http://www.orange-book.com/>

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes