

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Rubber Whetstone with Shaft (shaft diameter 6mm)



CH820C (#80, brown)



MI1220M (#120, green)



KI2220F (#220, yellow)

Estimated Unit Price per Piece
¥334 to ¥537

- Features**
- Demonstrates high cutting performance without clogging even with SUS-based steel materials.
 - High cutting performance even at a low speed rotation range.
 - Sintered with WA + polycrystalline porous abrasives.
- Use**
- Ideal for burr removal and cutting work.
 - For polishing work of molds.
- Origin** • Japan



#80 Series/Color: Brown

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
374-9711	CH815C	¥1,666	¥1,800	80	15 x 20 x 6 x 35	20000	5	10	100
374-9720	CH820C	¥2,222	¥2,400	80	20 x 25 x 6 x 35	15000	5	10	160
374-9738	CH825C	¥2,685	¥2,900	80	25 x 25 x 6 x 35	12000	5	10	210

#120 Series/Color: Green

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
374-9771	MI1215M	¥1,666	¥1,800	120	15 x 20 x 6 x 35	20000	5	10	100
374-9789	MI1220M	¥2,222	¥2,400	120	20 x 25 x 6 x 35	15000	5	10	160
374-9797	MI1225M	¥2,685	¥2,900	120	25 x 25 x 6 x 35	12000	5	10	210

#220 Series/Color: Yellow

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Max Working Rotation Speed (rpm)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
374-9746	KI2215F	¥1,666	¥1,800	220	15 x 20 x 6 x 35	20000	5	10	100
374-9754	KI2220F	¥2,222	¥2,400	220	20 x 25 x 6 x 35	15000	5	10	160
374-9762	KI2225F	¥2,685	¥2,900	220	25 x 25 x 6 x 35	12000	5	10	210


Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 262 Items

Elastic Whetstone with Shaft "Polaco Diamond"

- Features**
- Elastic whetstones specialized in grinding and polishing of carbide alloys.
 - High quality diamonds carefully selected by insisting on the quality of the diamond abrasive grains are ideal for grinding and polishing work of carbide dies and carbide punches.
- Use**
- Removal of electric discharge machining surface of cemented carbide and mirror surface polishing.
- Origin** • Japan



PDS0615-0200FH



PDS0615-0400FH



PDS0615-1000FH



PDS0615-2000FH



PDS0615-3000FH



PDS0615-0600FH



PDS0615-0800FH



Order Unit: 1 Piece

SOWA CO.LTD.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Outer Diameter x W x Shaft Diameter x Shaft Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
787-5371	PDS0615-0200FH	¥3,147	-	200	6 x 15 x 3 x 35	15000	1	5
787-5380	PDS0615-0400FH	¥3,147	-	400	6 x 15 x 3 x 35	15000	1	5
787-5398	PDS0615-0600FH	¥3,147	-	600	6 x 15 x 3 x 35	15000	1	5
787-5401	PDS0615-0800FH	¥3,147	-	800	6 x 15 x 3 x 35	15000	1	5
787-5410	PDS0615-1000FH	¥3,147	-	1000	6 x 15 x 3 x 35	15000	1	5
787-5428	PDS0615-2000FH	¥3,147	-	2000	6 x 15 x 3 x 35	15000	1	5
787-5436	PDS0615-3000FH	¥3,147	-	3000	6 x 15 x 3 x 35	15000	1	5
787-5444	PDS1015-0200FH	¥7,035	-	200	10 x 15 x 3 x 35	15000	1	12
787-5452	PDS1015-0400FH	¥7,035	-	400	10 x 15 x 3 x 35	15000	1	12
787-5461	PDS1015-0600FH	¥7,035	-	600	10 x 15 x 3 x 35	15000	1	12
787-5479	PDS1015-0800FH	¥7,035	-	800	10 x 15 x 3 x 35	15000	1	12
787-5487	PDS1015-1000FH	¥7,035	-	1000	10 x 15 x 3 x 35	15000	1	12
787-5495	PDS1015-2000FH	¥7,035	-	2000	10 x 15 x 3 x 35	15000	1	12
787-5509	PDS1015-3000FH	¥7,035	-	3000	10 x 15 x 3 x 35	15000	1	12
787-5517	PDS1515-0200FH	¥16,663	-	200	15 x 15 x 6 x 45	15000	1	20
787-5525	PDS1515-0400FH	¥16,663	-	400	15 x 15 x 6 x 45	15000	1	20
787-5533	PDS1515-0600FH	¥16,663	-	600	15 x 15 x 6 x 45	15000	1	20
787-5541	PDS1515-0800FH	¥16,663	-	800	15 x 15 x 6 x 45	15000	1	20
787-5550	PDS1515-1000FH	¥16,663	-	1000	15 x 15 x 6 x 45	15000	1	20
787-5568	PDS1515-2000FH	¥16,663	-	2000	15 x 15 x 6 x 45	15000	1	20
787-5576	PDS1515-3000FH	¥16,663	-	3000	15 x 15 x 6 x 45	15000	1	20

Contact us: 075-334-5591 <http://www.sowakasei.com/>

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes