



Stock
38,650
Items

Cabtire Cable Secondary Side Wire (with holder and round terminal)



Holder
(with TEH-300)

TCT-2210KH

- Features** • Since it uses elastic and tough natural rubber, it is resistant to shock, wear, etc., especially the with-stand voltage characteristics are very excellent.
- Use** • As a secondary cable (welding side) of the arc welding machine.
- Materials** • Natural Rubber for Conductors, Conductors
- Accessories** • Welding Rod Holder (TEH-300)
• $\Phi 8$ Round Terminal (insulating cap)
- Origin** • Japan



Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Applicable Current (A)	Working Cable (mm ²)	Cable (m)	SPQ (set)	Weight (kg/set)
754-6751	TCT-2205KH	¥11,757	¥12,700	100 to 170	WCT-22	5	1	1.9
326-5935	TCT-2210KH	¥16,617	¥17,950	100 to 170	WCT-22	10	1	3.8
754-6777	TCT-3805KH	¥16,570	¥17,900	170 to 240	WCT-38	5	1	2.8
326-5943	TCT-3810KH	¥25,633	¥27,690	170 to 240	WCT-38	10	1	5.8

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock
38,650
Items


Cabtire Cable Secondary Side (with grounding clip and round terminal)



Grounding Clip
(with TEC-300)

TCT-2210KE

- Features** • Since it uses elastic and tough natural rubber, it is resistant to shock, wear, etc., especially the with-stand voltage characteristics are very excellent.
- Use** • As a secondary cable (for grounding) of the arc welding machine.
- Materials** • Natural Rubber for Conductors, Conductors
- Accessories** • Grounding Clip (TEC-300)
• $\Phi 8$ Round Terminal (insulating cap)
- Origin** • Japan



Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Applicable Current (A)	Working Cable (mm ²)	Cable (m)	SPQ (set)	Weight (kg/set)
754-6742	TCT-2205KE	¥12,312	¥13,300	100 to 170	WCT-22	5	1	2.0
326-5951	TCT-2210KE	¥16,996	¥18,360	100 to 170	WCT-22	10	1	3.8
754-6769	TCT-3805KE	¥17,033	¥18,400	170 to 240	WCT-38	5	1	2.9
326-5960	TCT-3810KE	¥26,133	¥28,230	170 to 240	WCT-38	10	1	5.8

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock
38,650
Items

Cabtire Cable Secondary Side (with holder and cable joint)



Holder
(with TEH-300)

TWC-225KH

Cable Joint
(with TKJ-300 male)

- Features** • Since it uses elastic and tough natural rubber, it is resistant to shock, wear, etc., especially the with-stand voltage characteristics are very excellent.
- Use** • As a secondary cable (welding side) of the arc welding machine.
- Materials** • Conductor part: Copper wire
• Coating: Natural Rubber for Conducting Wire
- Accessories** • Welding Rod Holder (TEH-300)
• Cable Joint (TKJ-300 male)
- Origin** • Japan



Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Applicable Current (A)	Working Cable (mm ²)	Cable (m)	SPQ (set)	Weight (kg/set)
273-1053	TWC-225KH	¥13,164	¥14,220	100 to 170	WCT-22	5	6	2.1
273-1061	TWC-2210KH	¥18,061	¥19,510	100 to 170	WCT-22	10	1	3.6
352-3608	TWC-385KH	¥19,385	¥20,940	170 to 240	WCT-38	5	5	3.0
352-3683	TWC-3810KH	¥30,863	¥33,340	170 to 240	WCT-38	10	1	5.3

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock
38,650
Items

Cabtire Cable Secondary Side (with grounding clip and cable joint)



Grounding Clip
(with TEC-300)

TWC-225KE

Cable Joint
(with TKJ-300 male)

- Features** • Since it uses elastic and tough natural rubber, it is resistant to shock, wear, etc., especially the with-stand voltage characteristics are very excellent.
- Use** • As a secondary cable (for grounding) of the arc welding machine.
- Materials** • Conductor part: Copper wire
• Coating: Natural Rubber for Conducting Wire
- Accessories** • Grounding Clip (TEC-300)
• Cable Joint (TKJ-300 male)
- Origin** • Japan



Order Unit: 1 Set

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Applicable Current (A)	Working Cable (mm ²)	Cable (m)	SPQ (set)	Weight (kg/set)
273-1096	TWC-225KE	¥13,460	¥14,540	100 to 170	WCT-22	5	6	2.1
273-1100	TWC-2210KE	¥18,561	¥20,050	100 to 170	WCT-22	10	1	3.6
352-3594	TWC-385KE	¥19,782	¥21,370	170 to 240	WCT-38	5	5	3.1
352-3560	TWC-3810KE	¥31,150	¥33,650	170 to 240	WCT-38	10	1	5.4

Contact us:0120-509-849 <http://www.orange-book.com/>