

DOUBLE SPIRAL BRUSHES STAINLESS STEEL


## ダブルスパイラルブラシ

ステンレス

φ6mm



サイズ Size (mm) A×B×C×D	タイプ Type	品番 NO.	入数 Pack	MAX min <sup>-1</sup>	Price ¥ (1個単価)
10×50×6×60	SUS φ0.12	BSNSD-10	10個	2,600	2,880
15×50×6×60		BSNSD-15		1,950	3,000
20×50×6×60		BSNSD-20		1,700	3,200
25×50×6×60		BSNSD-25		1,350	3,400
30×50×6×60		BSNSD-30		1,100	3,600
40×50×6×60	SUS φ0.15	BSNSD-40	10個	720	3,800
50×50×6×60		BSNSD-50		520	4,000



超硬


W ROLLS CONDENSER BRUSHES STAINLESS STEEL

## W巻コンデンサーブラシ

ステンレス

φ6mm

サイズ Size (mm) A×B×C×D	タイプ Type	品番 NO.	入数 Pack	MAX min <sup>-1</sup>	Price ¥ (1個単価)
10×50×6×60	SUS φ0.15	BSCD-101	10個	2,600	1,790
13×50×6×60		BSCD-102		1,950	1,710
16×50×6×60		BSCD-103		1,700	
19×50×6×60		BSCD-104		1,350	1,820
25×50×6×60		BSCD-105		780	1,960
32×50×6×60		BSCD-106		720	2,120
38×50×6×60		BSCD-107		520	2,270
50×50×6×60		BSCD-108			



ダイヤ

砥石

ペーパー

ナイロン

ブラシ

MINI TWIST BRUSHES STAINLESS STEEL


## ミニ軸付ネジリブラシ

ステンレス

φ3mm



サイズ Size (mm) A×B×C×D	タイプ Type	品番 NO.	入数 Pack	MAX min <sup>-1</sup>	Price ¥ (1個単価)
1×20×3×50	SUS φ0.06	BMNS-0103	10個	1,200	4,800
1.5×20×3×50		BMNS-0153			
2×25×3×45		BMNS-0203			
2.5×25×3×45	SUS φ0.08	BMNS-0253	10個	1,200	4,600
3×30×3×40		BMNS-0303			



パフ

W ROLLS CONDENSER BRUSHES BRASS

## W巻コンデンサーブラシ

真鍮

φ6mm

サイズ Size (mm) A×B×C×D	タイプ Type	品番 NO.	入数 Pack	MAX min <sup>-1</sup>	Price ¥ (1個単価)
10×50×6×60	真鍮 φ0.15	BMCD-111	10個	2,600	1,790
13×50×6×60		BMCD-112		1,950	1,710
16×50×6×60		BMCD-113		1,700	
19×50×6×60		BMCD-114		1,350	1,820
25×50×6×60		BMCD-115		780	1,970
32×50×6×60		BMCD-116		720	2,120
38×50×6×60		BMCD-117		520	2,270
50×50×6×60		BMCD-118			

