

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items** **Welder Connection Cable Joint (with terminal)**



TWC-22J

**Features** • It is easy to attach and detach the wire to the secondary side terminal of the welding equipments.  
**Specs** • Connection Application: Cable + Welding Machine  
**Origin** • Japan



Item No.	Terminal Size
TWC-22J	22-8
TWC-38J	38-10

Order Unit: 1 Piece (Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Welding Current (A)	Working Cable (mm <sup>2</sup> )	Total Length (mm)	SPQ (piece)	Weight (g)
270-7969	TWC-22J	¥2,323	¥2,510	100 to 200	22	235	50	210
352-4523	TWC-38J	¥2,731	¥2,950	100 to 300	38	230	50	247

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items** **Plug-in Metal Fitting**



HW-SK

**Features** • For marking on welds, metal plates and building materials.  
**Specs** • Connection Application: Cable + Welding Machine  
**Accessories** • Hexagonal wrench  
**Origin** • Japan


**Warning**  
 • This type is directly attached to the female side terminal of the welding equipments.  
 • Cable joint cannot be connected with TKJ-300.

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Welding Current (A)	Working Cable (mm <sup>2</sup> )	Total Length (mm)	SPQ (piece)	Weight (g)
310-4788	HW-SK	¥1,666	¥1,800	100	22	135	10	90

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items** **Copper Pipe Sleeve**



TPS-22SQ

**Features** • Copper pipe sleeve for wire connection.  
**Origin** • Japan



TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Bag



TPL-22SQ

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Size (mm)	Compatible Commodity	Qty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
402-6624	TPS-22SQ	¥ 806	¥ 870	φ10.0 x 26	TKJ-300/HW-SK	10	10	29
402-6586	TPL-22SQ	¥ 806	¥ 870	φ10.0 x 35	TEH-300/TEC-300/TEC-300A	10	10	37
402-6632	TPS-38SQ	¥ 806	¥ 870	φ11.0 x 26	TKJ-300	10	10	32
402-6594	TPL-38SQ	¥ 806	¥ 870	φ11.0 x 35	TEH-300/TEC-300/TEC-300A	10	10	40
402-6641	TPS-50SQ	¥1,055	¥1,140	φ11.8 x 29	TKJ-300/TEC-300G	10	10	36
402-6608	TPL-50SQ	¥1,055	¥1,140	φ11.8 x 38	TEH-300/TEC-300/TEC-300A	10	10	45
402-6659	TPS-60SQ	¥ 703	¥ 760	φ13.8 x 34	TKJ-500/TEC-500G	5	10	27
402-6616	TPL-60SQ	¥ 703	¥ 760	φ13.8 x 48	TEH-500	5	10	35

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items** **Connector Terminal**



HW-22SK

**Features** • Because it is bolted, easy to connect.  
 • Used to connect cables to welding equipments.  
**Specs** • Connection Application: Cable + Welding Machine  
**Origin** • Japan

Item No.	Total Length (mm)	Terminal Size
HW-22SK	36.5	22-10
HW-38SK	42.5	38-12

**Warning**  
 • There may be some errors in the total length for manufacturing reasons.

Order Unit: 1 Bag TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Welding Current (A)	Working Cable (mm <sup>2</sup> )	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
310-4362	HW-22SK	¥768	¥ 830	100 to 200	22	2	10	70
310-4397	HW-38SK	¥926	¥1,000	100 to 300	38	2	10	115


Contact us:0120-509-849 <http://www.orange-book.com/>

ASADA **Stock 459 Items** **Rotary Grounding Clamp**



S780435

**Features** • You can fix in two directions.  
 • Used to prevent corrosion of the grounding cord during arc welding.  
**Specs** • Pinching Capacity: 20mm  
**Origin** • USA



Order Unit: 1 Piece (Price revision date: Jun, 2017) ASADA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Welding Current (A)	Working Cable (mm <sup>2</sup> )	Total Length (mm)	SPQ (piece)	Weight (kg)
376-0499	S780435	¥20,790	¥22,000	400	22 to 60	150	1	1.8

Contact us:052-911-7165 <http://www.asada.co.jp/>