

# Bearing Cover Plates

## Standard




RoHS10


Flat		Pilot		Material	Surface Treatment
Round Flanged	Square Flanged	Round Flanged	Square Flanged		
-	BVFS	-	BVIS	S45C	-
BVFCM	BVFSM	BVICM	BVISM	S45C	Electroless Nickel Plating
-	-	BVICA	BVISA	A5052	Clear Anodize
BVFC	-	-	-	SUS304	-

6.3 / ( 1.6 / )

### Flat



### Pilot



Part Number	Type	V	Applicable Bearing	Applicable Screw	H	P.C.D.	W	T	d	d1	D	S	Unit Price																			
													Flat				Pilot															
													Round Flanged	Square Flanged	Round Flanged	Square Flanged	Round Flanged	Square Flanged	Round Flanged	Square Flanged												
														BVFCM	BVFC	BVFS	BVFSM	BVICM	BVICA	BVIS	BVISM	BVISA										
	Flat (Round Flanged)	4	673	M3	26	16	21	5	3.5	6.5	6	1.5																				
		5	674																													
		6	693																													
		8	623, 694																													
		10	624, 695	M4	35	24	28	6	4.5	8.0	13	2.0																				
		11	605, 696																													
		12	625																													
		13	606																													
	(Square Flanged)	15	626, 698	M5	46	35	36	7	5.5	9.5	17	2.0																				
		18	608, 6900																													
		20	628, 6901																													
		21	6000																													
	Pilot (Round Flanged)	23	6001, 6902	M6	89	75	68	8	6.5	11.0	26	2.0																				
		25	6200, 6903																													
		26	6201, 6002																													
		30	6202, 6003																													
	(Square Flanged)	32	6904, 6203	M6	107	93	81	8	6.5	11.0	32	2.0																				
		35	6004, 6905																													
		40	6204, 6005, 6906																													
		46	6205																													
		47	6006, 6907																													
		56	6206, 6007, 6908																													
		64	6008, 6207, 6208																													



Ordering Example

Part Number

BVFS10



Alterations



Part Number - (FC, MXC, NC)

BVFCM10 - FC3-NC

Alterations	Blind Hole	Number of Mounting Holes	Mounting Hole Type
Code	FC	MXC	NC
Spec.	Changes V hole to blind hole. FC=1mm Increment 3 ≤ FC ≤ T-1 Ordering Code FC4	The number of mounting holes is changed from 4 to 6. Available for Round Flange Type only. Ordering Code MXC	Changes mounting holes to through holes. Hole Dia. = d (Specification Table) Ordering Code NC