


Pre-Assembly Insertion Nuts / Stoppers for Aluminum Extrusions - Others

For 5 Series (Slot Width 6mm)



Pre-Assembly Insertion Lock Nut **HNTC5**

Reference Tightening Torque (N · m)
M S10C Equivalent
 5 6.8

M Material: S10C Equivalent
S Surface Treatment: Trivalent Chromate **RoHS10**

ex **Pre-Assembly Insertion Lock Nut**
 The position of post-assembly insertion lock nuts can be fixed temporarily with the set screw.

Pre-Assembly Insertion Lock Nut HNTC
 Pre-Assembly Insertion Lock Nut HNTC
 Screw
 Plate
 Set Screw Temporarily held with a set screw.
 Aluminum Extrusions & Brackets

Ordering Example **Part Number** - **M**
HNTC5 - **5**

Part Number	M	Accessory	Unit Price	Volume Discount Rate		
			1 - 499 pc(s)	500-749	750-999	1000-1500
HNTC5	5	M4x4 Set Screw for Locking 1 pc.				

• Overall length is shorter than Pre-Assembly Insertion Nuts HNTT.
 Suitable for installing sensors or other components closely together.
 • Stopper is not included.

Pre-Assembly Insertion Short Nuts **HNTJ5 PACK-HNTJ5**

Reference Tightening Torque (N · m)
M S10C Equivalent
 5 6.8

M Material: S10C Equivalent
S Surface Treatment: Trivalent Chromate

Ordering Example **Part Number** - **M**
HNTJ5 - **5**

Part Number	M	HNTJ5			PACK-HNTJ5			
		Unit Price	Volume Discount Rate		Unit Price	Volume Discount Rate		
		1 - 499 pc(s)	500-749	750-999	1000-1500	1 - 9 pkg(s)	10-19	20-30
HNTJ5 PACK-HNTJ5	3 4 5							

100 pcs. per package

Pre-Assembly Insertion Square Nuts **HNKK5**

M Material: SPCC **S** Surface Treatment: Trivalent Chromate **RoHS10**

ex **Pre-Assembly Insertion Nuts**

HNKK

Ordering Example **Part Number** - **M**
HNKK5 - **5**

Part Number	M	Unit Price	Volume Discount Rate	
		1 - 9 pkg(s)	10-19	20-30
HNKK5	3 4 5			

100 pcs. per package

Metal Stoppers for Pre-Assembly Insertion Square Nuts **HNKKST5**

M Material: SUS301 **RoHS10**

ex

HNKK
 HNKKST

Ordering Example **Part Number**
HNKKST5

Part Number	Applicable Pre-Assembly Insertion Nut	Unit Price	Volume Discount Rate	
		1 - 9 pkg(s)	10-19	20-30
HNKKST5	HNKK5			

100 pcs. per package

Pre-Assembly Insertion Nuts Stainless Steel Sheet Metal Type **HNTTBSS5**

(SUS304) **RoHS10**

M	T	D
3	2.7	4.3
4	3.4	5.6
5	3.7	6.7

M Material: SUS304

Ordering Example **Part Number** - **M**
HNTTBSS5 - **5**

Part Number	M	E	T	Unit Price	Volume Discount Rate		
				1 - 499 pc(s)	500-749	750-999	1000-1500
HNTTBSS5 (SUS304)	3 4 5	2.0	Above Table				