



Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

Post-Assembly Insertion Nuts for Aluminum Extrusions - Others For 6 Series (Slot Width 8mm)




Tightening Torque **P526**

Post-Assembly Insertion Lock Nuts with Leaf Springs **RoHS 10**



Part	Material	Surface Treatment
Main Body	S10C Equivalent	Trivalent Chromate
Wing Part	SUS304	-

HNTRP6



Reference Tightening Torque (N·m)	
M	S10C Equivalent
6	11.7

Part Number	M	Accessory	Unit Price	Volume Discount Rate		
			1 ~ 499 pc(s).	500~749	750~999	1000~1500
HNTRP6	6	M4x4 Set Screw for Locking 1 pc.				

Post-Assembly Insertion Lock Nuts


RoHS 10



* Electrically conductive

Type	Material	Surface Treatment
HNTR6, HNTRZ6	S10C Equivalent	Trivalent Chromate
HNTRSNG*	SUS316 Equivalent (Sintered)	-

HNTR6 (S10C Equivalent)
HNTRSNG (SUS316 Equivalent, Sintered)
HNTRZ6 (Thread Locking, S10C Equivalent)



Reference Tightening Torque (N·m)	
M	S10C Equivalent / SUS316 Equivalent (Sintered)
6	11.7

Part Number	M	Accessory	Unit Price	Volume Discount Rate		
			1 ~ 499 pc(s).	500~749	750~999	1000~1500
HNTR6 (S10C Equivalent)	3 4 5 6	M4x6 Set Screw for Locking 1 pc.				
HNTRSNG (SUS316 Equivalent, Sintered)						
HNTRZ6 (Thread Locking, S10C Equivalent)			6			




Ordering Example

Part Number - M
HNTR6 - 6




Example

Post-Assembly Insertion Lock Nut (HNTR)




The nut can be fixed in place by itself by tightening the included set screw.



Suitable for use where high repeatability is required, such as mounting sensors or repeatedly replacing panels.


Post-Assembly Insertion Lock Nut with Leaf Springs (HNTRP)



Welded Leaf Springs prevents nuts from slipping off even if inserted into the vertically-oriented extrusions, leading to easy locating.


Also, the nut can be fixed in place by tightening the included set screw.

Post-Assembly Insertion Short Nuts



Part	Material	Surface Treatment
Main Body	S10C Equivalent	Trivalent Chromate
Wing Part	SUS301	-

HNTAJ6
PACK-HNTAJ6 (100/pkg.)



• Overall length is shorter than Pre-Assembly Insertion Nuts HNTT. Suitable for installing sensors or other components closely together.



Ordering Example Part Number - M
HNTAJ6 - 6

Part Number	M	HNTAJ6				PACK-HNTAJ6			
		Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
		1 ~ 499 pc(s).	500~749	750~999	1000~1500	1 pkg.	2~4	5~9	10~20
HNTAJ6 PACK-HNTAJ6	3 4 5 6								

100 pcs. per package