



Round Bar Pull Handles with Washers / Pull Handles with Rubber Grip



RoHS 10

Type	Material	Surface Treatment
① UWANZ	SUM22L or SUM24L	Chrome Plating
② UWANKZ	SUM22L or SUM24L	Black Oxide
③ UWANSZ	SUS304	Buffing
④ UWANAZ	SUM22L or SUM24L	Buffing
⑤ UWANEAZ	Aluminum Alloy	Clear Anodize
⑥ UWANBZ	SUM22L or SUM24L	Electrostatic Paint (Mat Black)




* Refer to Washers for Pull Handles below for washer details.

Part Number Type	D	L	H	Washer Selection	L ₁	Allowable Load (N)	Unit Price					
							UWANZ	UWANKZ	UWANSZ	UWANAZ	UWANEAZ	UWANBZ
UWANZ UWANKZ UWANSZ UWANAZ UWANEAZ UWANBZ	10	80	27	G SUM22L (Chrome Plating) B SUM22L (Electrostatic Paint, Black) S (SUS304)	90	2500						
			50									
		100	27									
			50									
		110	27									
			50									
		120	27									
			50									
		125	27									
			50									
160	27											
	50											
200	27											
	50											
250	27											
	50											



Type	Material	Surface Treatment
No Washer	SUS304 + Rubber	Buffing
With Washers		
UWANSL	SUM22L or SUM24L + Rubber	Chrome Plating
UWANL		

Rubber wrapped handle helps easy grip.



* Refer to Washers for Pull Handles below for washer details.


Part Number Type	D	L	H	Washers Selection for With Washer Type	L ₁	M	A	(t)	Allowable Load (N)	Unit Price					
										UWANL	UWANSL	UWANLZ	UWANSLZ		
UWANL UWANSL UWANLZ (With Washers) UWANSLZ (With Washers)	10	80	27	G SUM22L (Chrome Plating) B SUM22L (Electrostatic Paint, Black) S (SUS304)	90	5	50	11.5	2500						
			50												
		100	27												
			50												
		110	27												
			50												
		120	27												
			50												
		125	27												
			50												
	160	27													
		50													
	200	27													
		50													
	250	27													
		50													
12	150	40			162	8	120	13.5							
		75													
	188	40			200			158							
		75													
	238	40			250			208							
		75													
288	40			300		258									
	75														

Ordering Example	Part Number	L	H	Washer Selection
	UWANZ10	100	50	G
	UWANLZ10	100	27	G




Type	Material	Surface Treatment
UZG	SUM24L	Chrome Plating
UZB	SUM24L	Electrostatic Paint (Mat Black)
UZS	SUS304	Barrel Finishing

Available for round bars of Ø10 only.



Part Number	Unit Price
UZG	
UZB	
UZS	

Example



Ordering Example	Part Number
	UZG