



Reducing Tees

TS Fittings
PVCTTD



M Material: PVC

Part Number		Z ₁	Z ₂	H	I	Standards	Unit Price
Type	No.						1 ~ 50 pcs.
PVCTTD	1613	11	12	41	38	JIS K 6743	
	2016	13	15	48	45		
	2516	13	18	53	48		
	2520	15	18	55	53		
	3025	18	21	62	61		

For orders larger than indicated quantity, please check with WOS.

90° Elbows

Type	Types	M Material
PVCTE	TS Fittings	PVC
PVCHE	HI Fittings	Impact Resistance PVC



M Material: PVC

Part Number		Z	H	Standards	Unit Price	
Type	No.				PVCTE 1 ~ 50 pcs.	PVCHE 20 ~ 50 pcs.
PVCTE PVCHE	13	10	36	JIS K 6743		
	16	13	43			
	20	15	50			
	25	18	58			
	25	18	58			
	30	21	65			

For orders larger than indicated quantity, please check with WOS.

45° Elbows

HI Fittings
PVCHHE



M Material: Impact Resistance PVC

Part Number		Z	H	Standards	Unit Price
Type	No.				1 ~ 50 pcs.
PVCHHE	13	7	33	JIS K 6743	
	20	9	44		
	25	11	51		

For orders larger than indicated quantity, please check with WOS.

Caps

Type	Types	M Material
PVCTC	TS Fittings	PVC
PVCHC	HI Fittings	Impact Resistance PVC



M Material: Impact Resistance PVC

Part Number		L	Standards	Unit Price	
Type	No.			PVCTC 1 ~ 50 pcs.	PVCHC 20 ~ 50 pcs.
PVCTC PVCHC	13	29	JIS K 6743		
	16	33.5			
	20	38.5			
	25	44			
	30	48			

For orders larger than indicated quantity, please check with WOS.

Elastic Fittings

TS Fittings
PVCTY



M Material: PVC

Part Number		D	t	L	B	W	Standards	Unit Price
Type	No.							1 ~ 10 pcs.
PVCTY	13	26	3	68	25	38	JIS K 6743	
	16	34	5.5	110	29	42	-	
	20	35	3.5	78	29	50	JIS K 6743	
	25	43	4	89	29	56	JIS K 6743	
	30	48	4	98	33.5	63	JIS K 6743	

For PVCTY16, the nut is round-shaped. For orders larger than indicated quantity, please check with WOS.
Fittings for absorbing expansion / contraction of PVC Pipe due to heat

Valves

TS Fittings
PVCTB

M Material: PVC

Part Number		D	ds	H	L	L ₁	Standards	Unit Price	Volume Discount Rate
Type	No.							1 ~ 9 pc(s).	10 ~ 30 pcs.
PVCTB	16	50	22	78	109	77	JIS K 6743		
	20	59	26	89.5	125	97			
	25	68	32	101	142	97			
	30	80	38	119	158	129			

For orders larger than indicated quantity, please check with WOS.

Adhesive

PVCTBN
(For PVC)

PVCHBN
(For Impact Resistance PVC)




RoHS10

Part Number		Weight by Volume (g)		Unit Price
Type	No.			1~20 pcs.
PVCTBN	100	100		
	500	500		

Part Number		Weight by Volume (g)		Unit Price
Type	No.			1~20 pcs.
PVCHBN	100	100		
	500	500		

For orders larger than indicated quantity, please check with WOS.

Ordering Example
Part Number
PVCHSB20
PVCHBN100