


PVC Pipes / PVC Fittings

TS Fittings / HI Fittings


For dimension of the junction on fittings, see Dimension Table in Overview on P.1286. For specifications / application of each material, see Overview in P.1286.

PVC Pipe



Type	Material	Standards	Color
PVCT	PVC	JIS K 6742	Gray
PVCH	Impact Resistance PVC		Blue Gray

63(✓)



Note that pipe O.D. may have some scratches or small flaws on its surface.



Part Number	Type	No.	L 1mm Increment	O.D.		Thickness		I.D. (Reference Value)	Unit Price							
				D	D Tolerance	t	t Tolerance		PVCT							
									L50~200	201~400	401~600	601~800	801~1000	1001~1250	1251~1500	
PVCT PVCH		13	50~1500	18	±0.2	2.5	±0.2	13								
		16		22	±0.2	3	±0.3	16								
		20		26	±0.2	3	±0.3	20								
		25		32	±0.2	3.5	±0.3	25								
		30		38	±0.3	3.5	±0.3	31								

The tolerance of L dimension will be +1 ~ 3 for 50 ~ 1000, +2 ~ 5 for 1001 ~ 1500. * The price of PVCH is the price in the table above plus JPY100.

Ordering Example: Part Number - L
PVCT20 - 1000

Sockets

Type	Types	Material
PVCTS	TS Fittings	PVC
PVCHS	HI Fittings	Impact Resistance PVC






Part Number	Type	No.	Z	L	Standards	Unit Price	
						PVCTS	PVCHS
						1 ~ 50 pcs.	20 ~ 50 pcs.
PVCTS PVCHS		13	5	57	JIS K 6743		
		16	7	67			
		20	7	77			
		25	7	87			
		30	7	95			

For orders larger than indicated quantity, please check with WOS.

Sockets for Valve Sockets

Type	Types	Material
PVCTSB	TS Fittings	PVC
PVCHSB	HI Fittings	Impact Resistance PVC






Part Number	Type	No.	R(PT)	d	B	L	Standards	Unit Price	
								PVCTSB	PVCHSB
								1 ~ 50 pcs.	20 ~ 50 pcs.
PVCTSB PVCHSB		13	1/2	13	24	50	JIS K 6743		
		16	1/2	13	29	57			
		20	3/4	18	33	64			
		25	1	23	40	71			
		30	1 1/4	31	46	80			

For orders larger than indicated quantity, please check with WOS.

Reducing Sockets

Type	Types	Material
PVCTSD	TS Fittings	PVC
PVCHSD	HI Fittings	Impact Resistance PVC






Part Number	Type	No.	Z	L	Standards	Unit Price	
						PVCTSD	PVCHSD
						1 ~ 50 pcs.	20 ~ 50 pcs.
PVCTSD PVCHSD		1613	5	61	JIS K 6743		
		2016	6	71			
		2516	15	85			
		2520	9	84			
		3025	9	93			

For orders larger than indicated quantity, please check with WOS.

Tees

Type	Types	Material
PVCTT	TS Fittings	PVC
PVCHT	HI Fittings	Impact Resistance PVC

Part Number	Type	No.	Z1	Z2	H	I	Standards	Unit Price	
								PVCTT	PVCHT
								1 ~ 50 pcs.	20 ~ 50 pcs.
PVCTT PVCHT		13	10	10	36	36	JIS K 6743		
		16	13	13	43	43			
		20	15	15	50	50			
		25	18	18	58	58			
		30	21	21	65	65			

For orders larger than indicated quantity, please check with WOS.