


Ring Tongue Terminals (continued)															Manual Hand Tools			Dies for Powered Tools (see Note 1 for Tool Options)	
Wire Size		Studsize		Standard Part Number	Width (W)		Length (L)		Color	Wire Barrel Min. Inside Dia		Also available in ⁴		Re-remarks	Certi-Crimp Hand Tool (best)	Tetra-Crimp Hand Tool (better)	Pro-Crimper (SDE) Hand Tool (good)	SDE Die Set (Premium)	SDE Die Set (Commercial)
AWG	mm ²	U.S.	mm		inch	mm	inch	mm		inch	mm	Tape & Reel	Small Pack						
		8	M4	34853	.375	9.53	1.098	27.89	●	.250	6.35	✓	✓	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		10		330518	.312	7.92	1.052	26.72	●	.230	5.84	✓	-	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		10		34854	.375	9.53	1.098	27.89	●	.250	6.35	✓	✓	A	59239-4	59824-1	58433-3	2063030-1	58423-1
			M5	160292	.374	9.50	1.098	27.90	●	.252	6.40	✓	-	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		1/4	M6	165035	.500	12.70	1.184	30.07	●	.267	6.78	✓	-	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		1/4	M6	34855	.531	13.49	1.327	33.71	●	.250	6.35	✓	✓	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		5/16	M8	34856	.531	13.49	1.327	33.71	●	.250	6.35	✓	✓	A	59239-4	59824-1	58433-3	2063030-1	58423-1
			M8	160296	.500	12.70	1.185	30.10	●	.248	6.30	-	-	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		3/8		34173	.593	15.06	1.421	36.09	●	.230	5.84	✓	✓	A	59239-4	59824-1	58433-3	2063030-1	58423-1
			M10	160300	.594	15.09	1.433	36.40	●	.248	6.30	-	-	A	59239-4	59824-1	58433-3	2063030-1	58423-1
		1/2	M12	34837	.750	19.05	1.594	40.49	●	.250	6.35	✓	✓	A	59239-4	59824-1	58433-3	2063030-1	58423-1
8	6.64 - 10.50	8	M4	52041	.478	12.14	1.586	40.28	●	.360	9.14	✓	-	C					
		10		52263	.431	10.95	1.556	39.52	●	.360	9.14	✓	-	B					
		10		52263-1	.431	10.95	1.576	40.03	●	.330	8.38	✓	-	B					
		1/4	M6	52041-1	.478	12.14	1.586	40.28	●	.360	9.14	✓	-	C					
		5/16	M8	52291	.587	14.91	1.696	43.08	●	.360	9.14	✓	-	C					
		3/8		52291-1	.587	14.91	1.696	43.08	●	.360	9.14	✓	-	C					
		1/2	M12	52262-1	.875	22.23	1.860	47.24	●	.330	8.38	-	-	A					
6	10.5 - 16.8	8	M4	52042-2	.500	12.70	1.869	47.47	●	.436	11.07	-	-	C					
		10		52265	.468	11.89	1.719	43.66	●	.436	11.07	✓	✓	B					
		1/4	M6	52042-1	.500	12.70	1.869	47.47	●	.436	11.07	-	-	C					
		5/16	M8	52264	.625	15.88	1.906	48.41	●	.450	11.43	-	-	B					
		3/8		52264-1	.625	15.88	1.906	48.41	●	.450	11.43	-	-	B					
		1/2	M12	52350	.815	20.70	1.851	47.02	●	.436	11.07	-	-	C					
4	16.8 - 26.7	10		52043-2	.546	13.87	1.948	49.48	●	.450	11.43	✓	-	B					
		1/4	M6	52043-3	.546	13.87	1.948	49.48	●	.450	11.43	✓	-	B					
		5/16	M8	52266	.679	17.25	2.014	51.16	●	.515	13.08	-	-	B					
		3/8		52266-4	.679	17.25	2.014	51.16	●	.450	11.43	✓	-	B					
2	26.7 - 42.4	1/4	M6	52267-1	.675	17.15	2.071	52.60	●	.560	14.22	-	-	B					
		1/4	M6	52267	.675	17.15	2.071	52.60	●	.632	16.05	-	-	B					
		5/16	M8	52044-1	.711	18.06	2.089	53.06	●	.632	16.05	-	-	B					
		3/8		52044-2	.711	18.06	2.089	53.06	●	.632	16.05	-	-	B					



Multiple Studsize Ring Tongue															Manual Hand Tools			Dies for Powered Tools (see Note 1 for Tool Options)	
Wire Size		Studsize		Standard Part Number	Width (W)		Length (L)		Color	Wire Barrel Min. Inside Dia		Also available in ⁴		Re-remarks	Certi-Crimp Hand Tool (best)	Tetra-Crimp Hand Tool (better)	Pro-Crimper (SDE) Hand Tool (good)	SDE Die Set (Premium)	SDE Die Set (Commercial)
AWG	mm ²	U.S.	mm		inch	mm	inch	mm		inch	mm	Tape & Reel	Small Pack						
22 - 16	0,26 - 1,65	6 - 10	M3,5 - M5	54774-1	.325	8.26	.969	24.61	●	.125	3.18	✓	-		47386	59824-1	58433-3	2063030-1	58423-1
16 - 14	1,04 - 2,62	6 - 10	M3,5 - M5	54775-1	.325	8.26	.969	24.61	●	.145	3.68	✓	-		47387	59824-1	58433-3	2063030-1	58423-1