

MODEL		SW-60KM	SW-150KM	SW-60KL	SW-150KL
kg	Weighing capacity	60	150	60	150
	Minimum display	0.02	0.05	0.02	0.05
		0.01 *	0.02 *	0.01 *	0.02 *
		0.005	0.01	0.005	0.01
lb	Weighing capacity	130	330	130	330
	Minimum display	0.05	0.1	0.05	0.1
		0.02*	0.05*	0.02*	0.05*
		0.01	0.02	0.01	0.02
oz	Weighing capacity	2100	5200	2100	5200
	Minimum display	1	2	1	2
		0.5*	1*	0.5*	1*
		0.2	0.5	0.2	0.5
lb-oz	Weighing capacity	130	330	130	330
	Minimum display	1	1	1	1
Number of samples		5 (can be changed to 10, 20, 50 or 100) pieces			
Maximum count		120,000 pcs	150,000 pcs	120,000 pcs	150,000 pcs
Minimum unit weight		0.0005 kg	0.001 kg	0.0005 kg	0.001 kg
Repeatability (Std. deviation)		0.01 kg	0.02 kg	0.01 kg	0.02 kg
Linearity		±0.02 kg	±0.05 kg	±0.02 kg	±0.05 kg
Sensitivity drift		±20 ppm / °C (5°C to 35°C / 41°F to 95°F)			
Display		Weight display: 7 segment LED display (character height 14.6 mm) Comparison results: red / yellow / green / yellow / red LED			
Display update		10 times per second			
Operating conditions		-10°C to 40°C / 14°F to 104°F			
Power supply		AC main (100 V to 240 V, 50/60 Hz, 20 VA) or optional SLA battery (continuous operation of 90 hours depending on how the scale is used)			
Weighing pan size		300 x 380 mm / 11.8 x 15.0 in.		390 x 530 mm / 15.4 x 20.9 in.	
Dimensions (Models with a display pole)		300 (W) x 601 (D) x 722.5 (H) mm 11.8 (W) x 23.7 (D) x 28.4 (H) in.		390 (W) x 751 (D) x 722.5 (H) mm 15.4 (W) x 29.6 (D) x 28.4 (H) in.	
Mass (approximately) (Models with a display pole)		13.0 kg / 28.7 lb		16.2 kg / 35.7 lb	
Calibration weight (factory setting)		60 kg 120 lb	150 kg 300 lb	60 kg 120 lb	150 kg 300 lb

* Factory setting

Options

HC-02i SLA Sealed Lead Acid battery (YUASA NP4-6 recommended)

SW-03 RS-232C / Relay output

SW-04 RS-422 / 485

Note: The options, SW-03 and SW-04, can not be used at the same time.