



製品仕様

- 材質 FC200(JIS G5501)
- 歯形、精度 並歯、JISN8級(旧JIS4級)
- 圧力角 20°
- 表面処理 無し
- 歯面仕上 切削
- 穴径公差 JIS H7級

MP=1.5

製品記号	モジュール	歯数	ピッチ円直径	歯先円直径	歯幅	穴径	ボス径	ウェブ厚	リム内径
	m	Z	P.C.D.	D	W	d	B	F	H
SFA1545	1.5	45	67.5	70.5	15	16	40	5	57.5
SFA1548	1.5	48	72	75	15	16	40	5	62
SFA1550	1.5	50	75	78	15	16	40	5	65
SFA1555	1.5	55	82.5	85.5	15	16	40	5	72.5
SFA1560	1.5	60	90	93	15	16	40	5	80
SFA1565	1.5	65	97.5	100.5	15	16	40	5	87.5
SFA1570	1.5	70	105	108	15	16	40	5	95
SFA1575	1.5	75	112.5	115.5	15	16	40	5	102.5
SFA1580	1.5	80	120	123	15	16	40	5	110
SFA1585	1.5	85	127.5	130.5	15	16	40	5	117.5
SFA1590	1.5	90	135	138	15	16	40	5	125
SFA1595	1.5	95	142.5	145.5	15	16	40	5	132.5
SFA15100	1.5	100	150	153	15	18	45	5	140
SFA15120	1.5	120	180	183	15	18	45	5	170

MP=2.0

製品記号	モジュール	歯数	ピッチ円直径	歯先円直径	歯幅	穴径	ボス径	ウェブ厚	リム内径
	m	Z	P.C.D.	D	W	d	B	F	H
SFA2040	2	40	80	84	20	18	50	6	68
SFA2045	2	45	90	94	20	18	50	6	78
SFA2048	2	48	96	100	20	18	50	6	84
SFA2050	2	50	100	104	20	20	50	6	88
SFA2055	2	55	110	114	20	20	50	6	98
SFA2060	2	60	120	124	20	20	50	6	108
SFA2065	2	65	130	134	20	20	50	6	118
SFA2070	2	70	140	144	20	20	50	6	128
SFA2075	2	75	150	154	20	20	50	6	138
SFA2080	2	80	160	164	20	20	55	6	148
SFA2085	2	85	170	174	20	20	55	6	158
SFA2090	2	90	180	184	20	20	55	6	168
SFA2095	2	95	190	194	20	20	55	6	178
SFA20100	2	100	200	204	20	22	55	6	187
SFA20120	2	120	240	244	20	22	60	7	219