

Welders•Solders

MINI MINI WELDER

JP

Order No.	Model No.	Specification	Dimensions (mm)	JPY	Ref.No
6-1033-11	UH-1Series	Body (capacity 1.25~45Ws)	180×180×138	¥ 110,000	026370
6-1033-12	UH-2003	Body (capacity 15~135Ws)	150×226×135	¥ 220,000	026370
6-1033-13	UH-2003S	Body (capacity (strong) 15~135Ws / (weak) 5~45Ws)		¥ 240,000	026370
6-1033-21	UHP-901	Gun Grip Type Electrode	φ9.5mm, Cable Length 1m	¥ 40,000	026370
6-1033-22	UHP-103	Electrode for Plates (small pen type)	φ4×26mm Tip 1R	¥ 50,000	026370
6-1033-23	UHP-303	Electrode for Plates (thick pen type)	φ8×26mm Tip 1R	¥ 58,000	026370
6-1033-24	UHP-102A	Tweezers Type Electrode	140mm (tip 25mm 1R)	¥ 45,000	026370
6-1033-25	UHP-MF01	Negative Pen Type Electrode	φ8×50mm (tip 2×9mm plane)	¥ 38,000	026370
6-1033-26	UHP-308	Clip Type Minus Electrode	Pinching 10mm, Cable Length 1m	¥ 16,000	026370

※ Also order electrodes in combination of body.
 ※ Please use with UHP-MF 01 and UHP-308, or with electrode for plate material.

Feature ● This is compact and light weight sport welder specially designed for welding of thermocouple, thin plates and wires. ● With short current application pulse, welder causes less problems of material burning/deformation and is suitable to welding of small parts.

Specification ● Welding Method : Electrostatic Heat Storage Method
 ● Welding Speed : UH-1011 / 10~17times/minute, UH-2003・2003S / 3.5~17times/minute (charge voltage : 300V) ● Max. Rated Input Power : 65VA ● Power Supply : AC Adapter included (AC100~240V) ● Welding Time : 1msec ● Body Weight : UH-1011 / 3.0kg, UH-2003・2003S / 3.8kg ● Accessory : Remote Foot Switch



SUPER SMALL SPOT WELDING EQUIPMENT

JP

Order No.	Model No.	Dimensions (mm)	JPY	Ref.No
1-8159-01	KTH-MWS	155×260×150	¥ 160,000	026385
1-8159-11	Handy Tweezers Electrode		¥ 16,000	026385
1-8159-12	Tungsten Electrode		¥ 16,000	026385

Feature ● It is with handle which can carry simply in light weight (approx. 5.4kg). ● Spot welding of accessories and thin metal can be performed safely and simply. ● By using a handy tweezers electrode (sold separately), welding from φ0.2mm or less~ φ0.05mm is possible. ● By using tungsten electrode (sold separately), welding of a copper material is possible.

Specification ● Power Supply : AC100V 50/60Hz ● Weight : 5.4kg ● Current Control Method : Thyristor Phase Control Method ● Processing Time Range : 2 Cycle Usually Sets Up ● Accessories : CrCu Electrode (Tip Dia. 1.5mm)



DESK SOLDER SMOKE FILTER

JP

Order No.	Model No.	Dimensions (mm)	Weight (g)	JPY	Ref.No
2-9927-01	FA400-01	166×113×212	910	¥ 10,050	026370
2-9927-11	Replacement Filter A1001	130×130×10	5sheets	¥ 2,100	026370

Feature ● Can be placed vertically or laterally. ● When placed laterally, the flow velocity increases and it powerfully absorbs the smoke around your hand. ● When placed vertically, it absorbs smoke from a wider area.

Specification ● Operating Air Volume : Vertical Layout / 1.0m³/min (50Hz)・1.1m³/min (60Hz), Lateral Layout / 0.4m³/min (50Hz)・0.5m³/min (60Hz) ● Power Supply : AC100V 50/60Hz (with 3-pin plug) ● Power Consumption : 13W (50Hz)・15W (60Hz) ● Accessories : Replacement Filter × 1sheet (A1001)



AIR PURIFIER

JP

Order No.	Model No.	Dimensions (mm)	JPY	Ref.No
1-3678-01	FA430-01	330×343×366 (Body)	¥ 118,000	026360
1-3678-11	Duct Set Square Type C1571	φ55×1200	¥ 14,000	026360
1-3678-12	Duct Set Round Type C1572		¥ 14,000	026360
1-3678-13	Prefilter (10sheets) A1572		¥ 3,800	026360
1-3678-14	Main Filter A1573		¥ 18,800	026360
1-3678-15	Cap B3619		¥ 800	026360

※ The duct set is not supplied to body.

Specification ● Max. Processing : Using one duct / 4.1m³/min (145cFm)・Using 2 duct / 4.7m³/min (167cFm) ● Trapping Efficiency : LOW・MEDIUM Mode / 0.3μm particles 99.97% or more, HIGH Mode / 0.3μm particles 99.96% or more ● Noise Level : 50dB ● Static Pressure : 1500Pa ● Function : Air Volume Control (LOW・MEDIUM・HIGH)・Filter Replacement Alarm ● Power Supply : AC100V 50/60Hz with 3-Pin Plug ● Power Consumption : 120W ● Weight : 7.5kg

Feature ● Lightweight, compact, easy to carry with handle.

<Duct Set> ● Duct is self-sustaining, bend-stretchable, and excellent in stability. ● When net is attached to nozzle, it prevents sucking of foreign matter near suction port. ● Square type is suitable for suction from side, round type is suitable for suction from above.

Set Contents

<FA430-01> ● Body ● Power Cord ● Main Filter (A1573) ● Pre-filter × 10 (A1572) ● Cap (B3619)
 <Duct Set> ● Duct (B3642) ● Adapter (B3620) ● Square Nozzle (B3622・C1571 only) ● Round Nozzle (B3623・C1572 only) ● Net (B3625)

