


ピンゲートリーマ Pin Gate Reamer



公差 (Tolerance)	R: $\begin{matrix} 0 \\ -0.1 \end{matrix}$	$\theta : \pm 5'$	d: h7
----------------	--	-------------------	-------

右刃右ネジレ8° 刃数:4 SKH56
Helix Angle-Right8° Number of Flute:4 HSS-Co.

先端 R	両角 (θ) Taper Angle	刃長 (ℓ) Length of Flutes	大径 (D2) Dia at Large End	全長 (L) Overall Length	柄径 (φd) Shank Dia.
0.5	1°	25	1.43	70	4
	2°	25	1.86	70	4
	3°	25	2.28	70	4
	4°	25	2.71	70	4
	5°	25	3.14	70	4
0.75	1°	30	2.01	80	6
	2°	30	2.52	80	6
	3°	30	3.03	80	6
	4°	30	3.54	80	6
	5°	30	4.06	80	6
1	1°	40	2.68	90	6
	1°	70	3.2	120	6
	1°	120	4.08	170	6
	2°	40	3.36	90	6
	2°	70	4.41	120	6
	2°	120	6.15	170	6
	3°	40	4.04	90	6
	3°	70	5.61	120	6
	3°	120	8.23	170	8
	4°	40	4.73	90	6
	4°	70	6.82	120	6
	4°	120	10.31	170	10
1.25	5°	40	5.41	90	6
	5°	70	8.03	120	8
	5°	120	12.39	170	12
	1°	60	3.53	110	6
	2°	60	4.55	110	6
1.5	3°	60	5.58	110	6
	4°	60	6.6	110	6
	5°	60	7.63	110	8
	1°	45	3.76	95	6
	1°	80	4.37	130	6
	1°	130	5.24	180	6
	2°	45	4.52	95	6
	2°	80	5.74	130	6
	2°	130	7.49	180	8
	3°	45	5.28	95	6
	3°	80	7.11	130	8
	3°	130	9.73	180	10
1.5	4°	45	6.04	95	6
	4°	80	8.48	130	8
	4°	130	11.98	180	12
	5°	45	6.8	95	6
	5°	80	9.86	130	10
	5°	130	14.22	180	12

先端 R	両角 (θ) Taper Angle	刃長 (ℓ) Length of Flutes	大径 (D2) Dia at Large End	全長 (L) Overall Length	柄径 (φd) Shank Dia.
2	1°	50	4.84	100	6
	1°	90	5.54	140	6
	1°	130	6.23	180	6
	2°	50	5.68	100	6
	2°	90	7.07	140	8
	2°	130	8.47	180	8
	3°	50	6.51	100	6
	3°	90	8.61	140	8
	3°	130	10.7	180	10
	4°	50	7.35	100	8
	4°	90	10.14	140	10
	4°	130	12.94	180	12
2.5	5°	50	8.19	100	8
	5°	90	11.68	140	12
	5°	130	15.18	180	16
	1°	60	6	110	6
	1°	100	6.7	150	6
	1°	150	7.57	200	8
	2°	60	7.01	110	8
	2°	100	8.4	150	8
	2°	150	10.15	200	10
	3°	60	8.01	110	8
	3°	100	10.11	150	10
	3°	150	12.73	200	12
2.5	4°	60	9.02	110	10
	4°	100	11.81	150	12
	4°	150	15.3	200	16