



BMC

BULKHEAD MALE CONNECTOR

隔壁ハーフユニオン(オス)



(METRIC)

(Unit:mm)

TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	D	E	F	G	H	PANEL HOLE SIZE	Max. Panel Thickness
3	1/8	BMC-3-1	45	11	15	2.5	14	12	38	8.5	10
4	1/8	BMC-4-1	52.8	11	15.3	3.5	17	14	45.5	11.5	13
4	1/4	BMC-4-2	54.8	13	15.3	3.5	17	14	47.5	11.5	13
6	1/8	BMC-6-1	52.9	11	15.4	5	17	14	45.5	11.5	13
6	1/4	BMC-6-2	54.9	13	15.4	5	17	14	47.5	11.5	13
8	1/8	BMC-8-1	54.8	11	16.8	6	17	15.87	47	13.2	13.5
8	1/4	BMC-8-2	56.8	13	16.8	6	17	15.87	49	13.2	13.5
10	1/4	BMC-10-2	58.7	13	18.7	8	19	19	50	16.2	14.5
10	3/8	BMC-10-3	59.7	14	18.7	8	19	19	51	16.2	14.5
12	3/8	BMC-12-3	64.8	14	22.8	9.5	26	23	54	19.5	16
12	1/2	BMC-12-4	69.8	19	22.8	10	26	23	59	19.5	16

※管外径5φも製作しております。

(INCHES)



TUBE O.D. T	THREADS PT or NPT	PART. No.	A	B	D	E	F	G	H	PANEL HOLE SIZE	Max. Panel Thickness
1/8": 3.18	1/8	BMC-01-1	45	11	15	2.5	14	12	38	8.5	10
1/4": 6.35	1/8	BMC-02-1	52.9	11	15.4	5	17	14	45.5	11.5	13
1/4": 6.35	1/4	BMC-02-2	54.9	13	15.4	5	17	14	47.5	11.5	13
5/16": 7.94	1/4	BMC-025-2	56.8	13	16.8	6	17	15.87	49	13.2	13.5
3/8": 9.53	1/4	BMC-03-2	58.3	13	17.8	7	19	17.46	50	14.8	14.5
3/8": 9.53	3/8	BMC-03-3	59.3	14	17.8	7	19	17.46	51	14.8	14.5
1/2": 12.7	3/8	BMC-04-3	64.8	14	22.8	9.5	26	23	54	19.5	16
1/2": 12.7	1/2	BMC-04-4	69.8	19	22.8	10	26	23	59	19.5	16

A.D:FINGER TIGHT-±0.5mm (about)
※管外径3φも製作しております。

MC-PF

MALE CONNECTOR PF

ハーフユニオン(PF)



(METRIC)

(Unit:mm)

TUBE O.D. T	THREADS PF	PART. No.	A	B	C	D	E	F	G	H
3	1/8	MC-3-1PF	33	8	16	15	2.5	14	12	26
4	1/8	MC-4-1PF	35.3	8	18.3	15.3	3.5	14	14	28
6	1/8	MC-6-1PF	35.4	8	18.4	15.4	5	14	14	28
6	1/4	MC-6-2PF	39.4	12	18.4	15.4	5	19	14	32
8	1/8	MC-8-1PF	35.8	8	18.8	16.8	5	14	15.87	28
8	1/4	MC-8-2PF	39.8	12	18.8	16.8	6	19	15.87	32
10	1/4	MC-10-2PF	41.7	12	20.7	18.7	6	19	19	33
10	3/8	MC-10-3PF	41.7	12	20.7	18.7	8	22	19	33
10	1/2	MC-10-4PF	43.7	14	20.7	18.7	8	27	19	35
12	3/8	MC-12-3PF	43.8	12	22.8	22.8	8	22	23	33
12	1/2	MC-12-4PF	45.8	14	22.8	22.8	10	27	23	35

A.D:FINGER TIGHT-±0.5mm (about)
※管外径5φも製作しております。


使用する O RING

THREADS	O RING JIS B 2401
PF 1/8	P 8
PF 1/4	P 11
PF 3/8	P 14
PF 1/2	P 18


O RING は適用液体の種類によって材質を選択して下さい。

先端止りの場合B寸法

	B
PF 1/8	12
PF 1/4	15
PF 3/8	16
PF 1/2	19



先端止用



ガスケット用