


2 くい込み式管継手

溶接フレアドユニオン UW




継手の呼び	適用管外径A		E	D	六角対辺H	I	ℓ	手じめL(約)
	呼び径	外径						
UW - 6	6	6	4	16	14	7	74	95
UW - 8	8	8	6	16	17	7	74	95
UW - 10	10	10	8	19	19	7	74	97
UW - 12	12	12	10	20	22	7	74	97
UW - 15	15	15	12	26	27	7.5	78	103
UW - 16	16	16	13	28	30	7.5	78	103
UW - 18	18	18	14	28	32	8	78	103
UW - 20	20	20	17	32	36	8	78	103
UW - 22	22	22	18	32	36	9	78	103
UW - 25	25	25	20	38	41	10	78	105
UW - 28	28	28	22	39	46	10	82	110
UW - 30	30	30	25	46	46	10	82	111
UW - 32	32	32	26	46	50	11	82	111
UW - 35	35	35	28	46	55	11	82	117
UW - 38	38	38	32	55	60	12	82	121
UW - 40	40	40	32	55	60	12	90	129
UW - 50	50	50	40	65	75	12	90	133
UW - 1/8	1/8	10.5	8	19	19	7	74	97
UW - 1/4	1/4	13.8	11	22	24	7.5	78	102
UW - 3/8	3/8	17.3	14	28	32	8	78	103
UW - 1/2	1/2	21.7	18	32	36	9	78	103
UW - 3/4	3/4	27.2	22	39	46	10	82	110
UW - 1	1	34.0	28	46	55	11	82	117
UW - 1 1/4	1 1/4	42.7	34	58	65	12	90	131
UW - 1 1/2	1 1/2	48.6	40	65	75	12	90	133

※Average Values

※上記諸元は品質の向上により若干変わることがあります。

ハーフユニオン S



継手の呼び	適用管外径A		(PT) T	E	基準径の位置G	六角対辺		I	ℓ	手じめL(約)
	呼び径	外径				H ₁	H			
S - 4×1/8	4	4	1/8	2.5	3.97	12	12	6	22	25.5
S - 6×1/8	6	6	1/8	4	3.97	14	14	7	28	34.5
S - 6×1/4	6	6	1/4	4	6.01	14	14	7	33	37.5
S - 8×1/8	8	8	1/8	4	3.97	17	17	7	29	35.5
S - 8×1/4	8	8	1/4	6	6.01	17	17	7	33	37.5
S - 10×1/4	10	10	1/4	7	6.01	17	19	7	33	38.5
S - 10×3/8	10	10	3/8	8	6.35	19	19	7	34	39
S - 10×1/2	10	10	1/2	8	8.16	22	19	7	39	42.5
S - 12×1/4	12	12	1/4	7	6.01	19	22	7	33	38.5
S - 12×3/8	12	12	3/8	9	6.35	19	22	7	34	39
S - 12×1/2	12	12	1/2	10	8.16	22	22	7	39	42.5
S - 15×3/8	15	15	3/8	9	6.35	24	27	7.5	37	43
S - 15×1/2	15	15	1/2	12	8.16	24	27	7.5	41	45.5
S - 16×3/8	16	16	3/8	9	6.35	27	30	7.5	37	43
S - 16×1/2	16	16	1/2	12	8.16	27	30	7.5	41	45.5
S - 18×3/8	18	18	3/8	9	6.35	27	32	8	37	43
S - 18×1/2	18	18	1/2	12	8.16	27	32	8	41	45.5
S - 20×1/2	20	20	1/2	12	8.16	30	36	8	43	47.5
S - 20×3/4	20	20	3/4	16	9.53	30	36	8	45	48
S - 22×1/2	22	22	1/2	12	8.16	32	36	9	43	47.5
S - 22×3/4	22	22	3/4	16	9.53	32	36	9	45	48
S - 25×3/4	25	25	3/4	16	9.53	36	41	10	46	50
S - 25×1	25	25	1	20	10.39	36	41	10	49	52
S - 28×3/4	28	28	3/4	16	9.53	41	46	10	48	52.5
S - 28×1	28	28	1	22	10.39	41	46	10	51	54.5
S - 30×1	30	30	1	22	10.39	41	46	10	51	55
S - 30×1 1/4	30	30	1 1/4	25	12.70	46	46	10	55	57
S - 32×1 1/4	32	32	1 1/4	26	12.70	46	50	11	55	57
S - 35×1 1/4	35	35	1 1/4	28	12.70	46	55	11	55	60
S - 38×1 1/2	38	38	1 1/2	32	12.70	50	60	12	57	64
S - 40×1 1/2	40	40	1 1/2	32	12.70	55	60	12	62	69
S - 42×1 1/2	42	42	1 1/2	34	12.70	55	60	12	62	69
S - 50×2	50	50	2	40	15.88	65	75	12	71	76.5
S - 1/8×1/8	1/8	10.5	1/8	4	3.97	17	19	7	29	36.5
S - 1/8×1/4	1/8	10.5	1/4	7	6.01	17	19	7	33	38.5
S - 1/4×1/4	1/4	13.8	1/4	7	6.01	22	24	7.5	36	42
S - 1/4×3/8	1/4	13.8	3/8	9	6.35	22	24	7.5	37	42.5
S - 3/8×3/8	3/8	17.3	3/8	9	6.35	27	32	8	37	43
S - 3/8×1/2	3/8	17.3	1/2	12	8.16	27	32	8	41	45.5
S - 1/2×1/2	1/2	21.7	1/2	12	8.16	32	36	9	43	47.5
S - 1/2×3/4	1/2	21.7	3/4	16	9.53	32	36	9	45	48
S - 3/4×3/4	3/4	27.2	3/4	16	9.53	41	46	10	48	52.5
S - 3/4×1	3/4	27.2	1	22	10.39	41	46	10	51	54.5
S - 1×1	1	34.0	1	22	10.39	46	55	11	52	59
S - 1×1/4	1	34.0	1 1/4	28	12.70	46	55	11	55	60
S - 1 1/4×1 1/4	1 1/4	42.7	1 1/4	31	12.70	60	65	12	64	72
S - 1 1/4×1 1/2	1 1/4	42.7	1 1/2	34	12.70	60	65	12	64	72
S - 1 1/2×1 1/2	1 1/2	48.6	1 1/2	36	12.70	65	75	12	67	76
S - 1 1/2×2	1 1/2	48.6	2	40	15.88	65	75	12	71	76.5

※Average Values

※上記諸元は品質の向上により若干変わることがあります。