


## 8 くい込み式管継手

### ユニオンチース T




※Average Values

継手の呼び	適用品外径A		E	二面幅 h	六角対辺 H	I	ϕ	手締め L(約)
	呼び径	外径						
T-4	4		2.5	12	12	6	15	22.5
T-6	6		4	14	14	7	20	30.5
T-8	8		6	17	17	7	23	33.5
T-10	10		8	17	19	7	23	34.5
T-12	12		10	19	22	7	24	35.5
T-15	15		12	24	27	7.5	29	41.5
T-16	16		13	27	30	7.5	32	44.5
T-18	18		14	27	32	8	32	44.5
T-20	20		17	30	36	8	33	45.5
T-22	22		18	32	36	9	34	46.5
T-25	25		20	36	41	10	36	49.5
T-28	28		22	41	46	10	41	55.0
T-30	30		25	41	46	10	41	55.5
T-32	32		26	46	50	11	45	59.5
T-35	35		28	46	55	11	46	63.5
T-38	38		32	50	60	12	50	69.5
T-40	40		32	55	60	12	55	74.5
T-42	42		34	55	60	12	55	74.5
T-50	50		40	65	75	12	62	83.5
T-1/8	1/8	10.5	8	17	19	7	23	34.5
T-1/4	1/4	13.8	11	22	24	7.5	28	40.0
T-3/8	3/8	17.3	14	27	32	8	32	44.5
T-1/2	1/2	21.7	18	32	36	9	34	46.5
T-3/4	3/4	27.2	22	41	46	10	41	55.0
T-1	1	34.0	28	46	55	11	46	63.5
T-1 1/4	1 1/4	42.7	34	60	65	12	57	77.5
T-1 1/2	1 1/2	48.6	40	65	75	12	62	83.5

※上記諸元は品質の向上により若干変わることがあります。

### サービスチース(オス) FC



※Average Values

継手の呼び	適用品外径A		(PT) T	E	E1	基準径の 位置 G	二面幅 h	六角対辺 H	I	ϕ	手締め L(約)	L1 (約)
	呼び径	外径										
FC-4x1/8	4		1/8	2.5	4	3.97	12	12	6	15	22.5	13
FC-6x1/8	6		1/8	4	4	3.97	14	14	7	20	30.5	14
FC-6x1/4	6		1/4	4	7	6.01	17	14	7	23	33.5	17
FC-8x1/8	8		1/8	6	4	3.97	17	17	7	23	33.5	16
FC-8x1/4	8		1/4	6	7	6.01	17	17	7	23	33.5	18
FC-10x1/4	10		1/4	8	7	6.01	17	19	7	23	34.5	19
FC-10x3/8	10		3/8	8	9	6.35	19	19	7	24	35.5	19.5
FC-12x1/4	12		1/4	10	7	6.01	19	22	7	24	35.5	18
FC-12x3/8	12		3/8	10	9	6.35	19	22	7	24	35.5	20.5
FC-15x3/8	15		3/8	12	9	6.35	24	27	7.5	29	41.5	23.5
FC-15x1/2	15		1/2	12	12	8.16	24	27	7.5	29	41.5	26
FC-16x1/2	16		1/2	13	12	8.16	27	30	7.5	32	44.5	27
FC-18x1/2	18		1/2	14	12	8.16	27	32	8	32	44.5	30
FC-20x3/4	20		3/4	17	16	9.53	30	36	8	33	45.5	30.5
FC-22x3/4	22		3/4	18	16	9.53	32	36	9	34	46.5	32.5
FC-25x3/4	25		3/4	20	16	9.53	36	41	10	36	49.5	33.5
FC-25x1	25		1	20	22	10.39	36	41	10	36	49.5	35.5
FC-28x1	28		1	22	22	10.39	41	46	10	41	55	39.5
FC-30x1	30		1	25	22	10.39	41	46	10	41	55.5	39.5
FC-30x1 1/4	30		1 1/4	25	31	12.70	46	46	10	46	60.5	42.5
FC-32x1 1/4	32		1 1/4	26	31	12.70	46	50	11	46	60.5	43.5
FC-35x1 1/4	35		1 1/4	28	31	12.70	46	55	11	46	63.5	45.5
FC-38x1 1/2	38		1 1/2	32	36	12.70	50	60	12	50	69.5	48.5
FC-40x1 1/2	40		1 1/2	32	36	12.70	55	60	12	55	74.5	49.5
FC-50x2	50		2	40	46	15.88	65	75	12	62	83.5	58
FC-1/8x1/4	1/8	10.5	1/4	8	7	6.01	17	19	7	23	34.5	19
FC-1/4x3/8	1/4	13.8	3/8	11	9	6.35	22	24	7.5	28	40	22.5
FC-3/8x1/2	3/8	17.3	1/2	14	12	8.16	27	32	8	32	44.5	30
FC-1/2x3/4	1/2	21.7	3/4	18	16	9.53	32	36	9	34	46.5	32.5
FC-3/4x1	3/4	27.2	1	22	22	10.39	41	46	10	41	55	39.5
FC-1x1 1/4	1	34.0	1 1/4	28	31	12.70	46	55	11	46	63.5	45.5
FC-1 1/4x1 1/2	1 1/4	42.7	1 1/2	34	36	12.70	60	65	12	57	77.5	51.5
FC-1 1/2x2	1 1/2	48.6	2	40	46	15.88	65	75	12	62	83.5	58

※上記諸元は品質の向上により若干変わることがあります。