


4LF/4XLF 3S エンドミル 4枚刃 (ロング刃・特ロング刃)

SINCE 1935

F.K.D.®

4LF/4XLF 4-Flute Long Flute & Extra Long Flute End Mills

材質=HSS-Co(SKH56)
 刃数=4枚
 リード角=右振り30°
 刃径公差=0~+0.03
 (センター穴付)



○刃長が長く深溝・広幅の切削加工 再研磨が容易

Deep and Wide cut. Regrinding.

●注文例=型番、刃径、刃長、数量 「4LF 3x20」

※φ40径以上のサイズはシャンク径もご指定下さい。

型番	刃径(D)	刃長(l)	全長(L)	シャンク径(d)
4LF	3	20	58	6
4XLF	3	30	70	6
4XLF	3	40	80	6
4LF	3.1	20	58	6
4LF	3.2	20	58	6
4LF	3.3	20	58	6
4LF	3.4	20	58	6
4LF	3.5	25	63	6
4XLF	3.5	30	70	6
4XLF	3.5	40	80	6
4LF	3.6	25	63	6
4LF	3.7	25	63	6
4LF	3.8	25	63	6
4LF	3.9	25	63	6
4LF	4	25	63	6
4XLF	4	30	70	6
4XLF	4	40	80	6
4XLF	4	50	90	6
4LF	4.1	25	63	6
4LF	4.2	25	63	6
4LF	4.3	25	63	6
4LF	4.4	25	63	6
4LF	4.5	30	68	6
4XLF	4.5	40	80	6
4XLF	4.5	50	90	6
4LF	4.6	30	68	6
4LF	4.7	30	68	6
4LF	4.8	30	68	6
4LF	4.9	30	68	6
4LF	5	30	68	6
4XLF	5	40	80	6
4XLF	5	50	90	6
4XLF	5	60	100	6
4LF	5.1	30	68	6
4LF	5.2	30	68	6
4LF	5.3	30	68	6
4LF	5.4	30	68	6
4XLF	5.5	30	70	6
4LF	5.5	35	73	6
4XLF	5.5	40	80	6
4XLF	5.5	50	90	6
4XLF	5.5	60	100	6
4LF	5.6	35	73	6
4LF	5.7	35	73	6
4LF	5.8	35	73	6

型番	刃径(D)	刃長(l)	全長(L)	シャンク径(d)
4LF	5.9	35	73	6
4XLF	6	30	70	6
4LF	6	35	73	6
4XLF	6	40	80	6
4XLF	6	50	90	6
4XLF	6	60	100	6
4LF	6.1	35	73	6
4LF	6.2	35	73	8
4LF	6.3	35	73	8
4LF	6.4	35	73	8
4XLF	6.5	30	70	8
4LF	6.5	35	73	8
4XLF	6.5	40	80	8
4XLF	6.5	50	90	8
4XLF	6.5	60	100	8
4LF	6.6	35	73	8
4LF	6.7	35	73	8
4LF	6.8	35	73	8
4LF	6.9	35	73	8
4XLF	7	30	70	8
4LF	7	35	73	8
4XLF	7	40	80	8
4XLF	7	50	90	8
4XLF	7	60	100	8
4LF	7.1	35	73	8
4LF	7.2	35	73	8
4LF	7.3	35	73	8
4LF	7.4	35	73	8
4XLF	7.5	30	70	8
4LF	7.5	40	78	8
4XLF	7.5	50	90	8
4XLF	7.5	60	100	8
4XLF	7.5	80	120	8
4LF	7.6	40	78	8
4LF	7.7	40	78	8
4LF	7.8	40	78	8
4LF	7.9	40	78	8
4XLF	8	30	70	8
4LF	8	40	78	8
4XLF	8	50	90	8
4XLF	8	60	100	8
4XLF	8	80	120	8
4XLF	8	100	140	8
4LF	8.1	40	78	8
4LF	8.2	40	78	10