

Stainless steel knocker

Body, base, mounting bolts and other parts of RKVS series are made of stainless steel and suitable for food, chemical, and pharmaceutical industries where corrosion resistance and sanitation are required. Also, this model is suitable for industry related to rechargeable battery.



RKVS15



RKVS20



RKVS30



RKVS40



RKVS60

Hygienic knocker (Sanitary Tri-clamp)



RKVS15-F



RKVS20F



Tri-clamp
(standard accessory)

■ Specification (Metric)

| Model | Working Pressure (MPa) | Stroke Cycle (time/min) | Air Consumption (L/time) (ANR) | Stroke Energy (N·m) | Impulsive Force | | Weight (kg) |
|----------|------------------------|-------------------------|--------------------------------|---------------------|-----------------|---------------------------------|-------------|
| | | | | | (kg·m/s) | Converts into Hammer pound (lb) | |
| RKVS15 | 0.3~0.7 | 1~60 | 0.03~0.06 | 2.7~5.9 | 0.3~0.5 | Mini Hammer | 0.43 |
| RKVS15-F | | | | | | | 0.94 |
| RKVS20 | | | 0.04~0.10 | 4.3~8.3 | 0.6~0.8 | Below0.6 | 0.80 |
| RKVS20F | | | | | | | 0.90 |
| RKVS30 | | | 0.05~0.13 | 5.5~13.1 | 1.2~1.8 | Below1.0 | 1.60 |
| RKVS40 | | | 0.15~0.37 | 9.2~22.3 | 2.6~4.0 | 1.0~1.5 | 4.20 |
| RKVS60 | | | 0.33~0.77 | 20.6~49.0 | 6.9~10.6 | 1.5~3.0 | 10.40 |

■ Specification (Imperial)

| Model | Working Pressure (PSI) | Stroke Cycle (time/min) | Air Consumption (cf/time) | Stroke Energy (lbf·ft) | Impulsive Force | | Weight (kg)(lb) |
|----------|------------------------|-------------------------|---------------------------|------------------------|-----------------|---------------------------------|-----------------|
| | | | | | (ft·lbf/s) | Converts into Hammer pound (lb) | |
| RKVS15 | 44~102 | 1~60 | 0.001~0.002 | 2.0~4.4 | 2.2~3.6 | Mini Hammer | 0.9 |
| RKVS15-F | | | | | | | 2.1 |
| RKVS20 | | | 0.001~0.004 | 3.2~6.1 | 4.3~5.8 | Below0.6 | 1.8 |
| RKVS20F | | | | | | | 2.0 |
| RKVS30 | | | 0.002~0.005 | 4.1~9.7 | 8.7~13.0 | Below1.0 | 3.5 |
| RKVS40 | | | 0.005~0.013 | 6.8~16.4 | 18.8~28.9 | 1.0~1.5 | 9.3 |
| RKVS60 | | | 0.012~0.027 | 15.2~36.1 | 49.9~76.7 | 1.5~3.0 | 22.9 |

* Reinforcing rib is included in RKVS60 only, and fall prevention wire and shackle are included in RKVS20-60.

* F-type includes tri-clamp and stainless steel.

* Fall prevention wire for RKVS15-F and RKVS20F is optional.