


FUJILOK U-NUT Single Chamfer, Double Chamfer, Thin Type



● : Available

Thread Accuracy: ISO6H (JIS6H) Unit: mm

		Material of the Nut Body						SS400		S45C-H		SUS304		Unit Weight (g) Approx. (Except for the Thin Type)	
		Material of the Friction Ring						SUS301							
Nominal Diameter (d)	Pitch (p)	Width Across Flat (s)		Overall Height (h)		Thread Height (m) Approx.	Across Corners (e) Approx.	Single Chamfer	Double Chamfer	Thin Type (h1)	Double Chamfer	Thin Type (h1)	Single Chamfer		Thin Type (h1)
		Base	Tolerance	Base	Tolerance										
M 3	0.5	5.5		3.2		2.7	6.4		●				●		0.4
M 4	0.7	7	0	3.8	±0.3	3.0	8.1		●	3.1			●	3.1	0.8
M 5	0.8	8	-0.2	4.6		3.9	9.2		●	4.0	●		●	3.4	1.2
M 6	1	10		5.1		4.2	11.5		●	4.0	●		●	4.0	2.1
M 8	1.25	13	0	7.3		6.1	15.0		●	5.0	●		●	5.0	5.1
	1		-0.25						●	5.0	●		●		
M10	1.5	17		8.3	±0.4	7.1	19.6		●	6.5	●		●	6.5	10.0
	1.25								●	6.5	●	6.5	●	6.5	
	1.75								●	8.5	●	8.5	●	8.5	
M12	1.5	19		10.5		9.0	21.9		●	8.5	●		●		15.2
	1.25								●	8.5	●	8.5	●		
M14	2	22	0	12.5		11.0	25.4	●		9.5	●		●	9.5	24.0
	1.5		-0.35					●		9.5	●		●		
M16	2	24		14.5	±0.5	13.0	27.7	●		12.0	●	12.0	●	11.0	31.5
	1.5							●		12.0	●	12.0	●	11.0	
M18	2.5	27		16.0		14.0	31.2	●			●		●		45.2
	1.5							●		12.0	●	12.0	●	12.0	
M20	2.5	30		17.5		15.4	34.6	●		14.0	●		●	13.5	61.4
	1.5							●		14.0	●	12.0	●		
M22	2.5	32		19.5		17.2	37.0	●			●		●		74.3
	1.5							●		12.5	●		●		
M24	3	36	0	21.5	±0.6	18.8	41.6	●		16.0	●		●	16.5	108
	2		-0.4					●		16.0	●		●		
M27	3	41		24.0		21.2	47.3	●			●		●		159
M30	3.5	46		27.0	±0.8	24.0	53.1	●		21.0	●		●	21.0	226
	3							●			●		●		
M33	3.5	50		29.5		26.5	57.7	●			●		●		287
	3							●			●		●		
M36	4	55		32.5	±1	29.5	63.5	●			●		●		393
	3							●			●		●		
M39	4	60		35		31.8	69.3	●			●		●		509
	3							●			●		●		
M42	4.5	65	0	38	±1.5	34.5	75.0	●			●		●		651
	3		-0.45					●			●		●		
M45	4.5	70		40		36.0	80.8	●			●		●		794
	3					36.5		●			●		●		
M48	5	75		42		38.0	86.5	●			●		●		972
	3							●			●		●		
M52	5	80		46		42.0	92.4	●			●		●		1190
	3							●			●		●		
M55	3	85		49	±2	44.5	98.1	●			●		●		1360
	5.5							●			●		●		
M56	4					45.0		●			●		●		1410
	4							●			●		●		
M60	5.5	90	0	52		47.5	104.0	●			●		●		1660
	4		-0.55			48.0		●			●		●		
M64	6	95		54		50.0	110.0	●			●		●		1910
	4							●			●		●		

* Thin type (h1) mentioned is available. *Please confirm the shape on single or double chamfer.

* Please check the stock condition of each size. * The material also includes items with equivalent materials. * Dimensions may change for improvement.