


Body

Model No.	Blade	Dimensions(mm)	Guide plate overall length (mm)	Inserts	Weight
HAM4-150CP3003	3	W93×D205×H119	150	SDMW type or SDEW type	2kg


- ※ Insert is not equipped as standard accessory
- ※ Clamp screw and wrench are supplied as standard accessory

Standard Equipment

Dedicated Cutter (equipped with Body) 3Blade




Accessories




Options

Dedicated Cutter(option) 3Blade



Resin Guide Plate(Option)



Insert

Figure	Model number	Material	Blade shape	Coating	Usable corners	Quantity per box
	SDMW11T4AFEN12 ZB01N	Cermet	Honing edge	None	4	10
	SDEW11T4AFFN12 ZA10D	Carbide K10	Sharp edge	None	4	10
	SDMW11T4AFEN12 ZA20D	Carbide M20	Honing edge	None	4	10
	SDEW11T4AFFN12 ZA10DL	Carbide K10	Sharp edge	None	4	10
	SDMW11T4AFEN12 AC15D	Fine particles Carbide	Honing edge	AlCrN	4	10