

Number of contacts

5/0+

230/400 V
16 A



Identification	Wire cross section (mm ²)	Part number		Drawing Dimensions in mm
		male	female	
Han® Q, Crimp terminal <p>Please order crimp contacts separately.</p>		09 12 005 3001	09 12 005 3101	<p>Contact arrangement (view from termination side)</p>
Han E®, Crimp contact, gold plated contacts, contact resistance ≤1 mOhm 	0.14–0.37 0.5 0.75 1 1.5 2.5	09 33 000 6117 09 33 000 6122 09 33 000 6115 09 33 000 6118 09 33 000 6116 09 33 000 6123	09 33 000 6217 09 33 000 6222 09 33 000 6215 09 33 000 6218 09 33 000 6216 09 33 000 6223	
Han E®, Crimp contact, silver plated contacts, contact resistance ≤1 mOhm 	0.14–0.37 0.5 0.75 1 1.5 2.5	09 33 000 6127 09 33 000 6121 09 33 000 6114 09 33 000 6105 09 33 000 6104 09 33 000 6102	09 33 000 6227 09 33 000 6220 09 33 000 6214 09 33 000 6205 09 33 000 6204 09 33 000 6202	
Han E®, Relay contact, silver plated contacts, contact resistance ≤1 mOhm 	0.75–1 1.5 2.5	09 33 000 6109 09 33 000 6110 09 33 000 6111		<p>Stripping length 7.5 mm</p>
Han E®, F.O. contact <p>for 1 mm plastic fibre</p>		20 10 001 3311	20 10 001 3321	<p>Crimp zone</p>

Han Q

Identification	Wire gauge	Stripping length
no groove	0.14-0.37 mm ² AWG 26-22	7.5 mm
no groove	0.5 mm ² AWG 20	7.5 mm
1 groove*	0.75 mm ² AWG 18	7.5 mm
1 groove	1 mm ² AWG 18	7.5 mm
2 grooves	1.5 mm ² AWG 16	7.5 mm
3 grooves	2.5 mm ² AWG 14	7.5 mm
wide groove	3 mm ² AWG 12	7.5 mm
no groove	4 mm ² AWG 12	7.5 mm

* on the back crimp collar